



Everyday™ Cyan Toner by Xerox compatible with HP 971XL (CN626AE, CN626A, CN626AM), High capacity

Brand : Xerox Product family: Everyday Product code: 006R04596

Product name : Everyday™
Cyan Toner by Xerox compatible
with HP 971XL (CN626AE,
CN626A, CN626AM), High
capacity

Everyday™ Cyan Toner by Xerox compatible with HP 971XL (CN626AE, CN626A, CN626AM), High capacity

Everyday™ Cyan Toner by Xerox compatible with HP 971XL (CN626AE, CN626A, CN626AM), High capacity:

Being environmentally responsible is simply the best way to do business, because it positively impacts the health of our planet, your company and your people. Everyday Remanufactured Toner by Xerox has the lowest carbon footprint than any single-use toner cartridge. Because you shouldn't have to choose between doing your part to reduce your eco-impact and your toner costs. And compatibility with the most popular printer brands means you can enjoy benchmark Xerox quality and stewardship no matter what kind of printer you have.

Everyday™ Cyan Toner by compatible with HP 971XL (CN626AE, CN626A, CN626AM), High capacity. Black toner page yield: 6600 pages, Colour toner page yield: 6600 pages, Printing colours: Cyan, Quantity per pack: 1 pc(s)



Cut Toner Costs, Not Quality

Save big with 40-60% savings on major printer brands.

Features		Features	
Compatibility *	Laser MFP X451 Laser MFP X476 Laser MFP X551 Laser MFP X576	OEM code	CN626AE, CN626A, CN626AM
Quantity per pack *	1 pc(s)	Quantity per box	1 pc(s)
Colour toner cartridges quantity	1	Country of origin	China
Black toner page yield *	6600 pages	Weight & dimensions	
Colour toner page yield *	6600 pages	Weight	223 g
Type *	Compatible	Packaging data	
Printing colours *	Cyan	Package width	50 mm
Brand compatibility *	HP	Package depth	225 mm
Supply type *	Single pack	Package height	35 mm
Cartridge capacity	High (XL) Yield	Package weight	220 g
Replacement for	HP 971XL	Logistics data	
		Export Control Classification Number (ECCN)	EAR99
		Harmonized System (HS) code	84439990



0095205037555



095205037555



5715063347737

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.