



APC BV650I-MSX uninterruptible power supply (UPS) Line-Interactive 0.65 kVA 375 W 4 AC outlet(s)

Brand : APC

Product code: BV650I-MSX

Product name : BV650I-MSX




EASY UPS BV 650VA, AVR, Universal Outlet, 230V

APC BV650I-MSX. UPS topology: Line-Interactive, Output power capacity: 0.65 kVA, Output power: 375 W. AC outlets quantity: 4 AC outlet(s). Battery technology: Sealed Lead Acid (VRLA), Battery capacity: 7 Ah, Battery voltage: 12 V. Product colour: Black, Cable length: 1.5 m, International Protection (IP) code: IP20. Certification: CE



Features		Design	
UPS topology *	Line-Interactive	Cable length	1.5 m
Output power capacity *	0.65 kVA	Product colour *	Black
Output power *	375 W	LED indicators	✓
Waveform *	Stepwise	International Protection (IP) code	IP20
Input operation voltage (min) *	170 V	Operational conditions	
Input operation voltage (max) *	280 V	Operating temperature (T-T)	0 - 40 °C
Input frequency *	50/60 Hz	Storage temperature (T-T)	-20 - 50 °C
Output frequency	50/60 Hz	Operating relative humidity (H-H)	0 - 90%
Automatic Voltage Regulation (AVR)	✓	Operating altitude	0 - 2032.1 m
Surge energy rating	156 J	Non-operating altitude	0 - 15240 m
Response time	6 ms	Certificates	
Noise level	40 dB	Certification	CE
Surge protection	✓	Weight & dimensions	
Power protection features	Over voltage, Overload, Short circuit, Under voltage	Width	165 mm
Audible alarm(s)	✓	Depth	305 mm
Ports & interfaces		Height	93 mm
AC outlets quantity	4 AC outlet(s)	Weight	4.5 kg
Battery		Packaging data	
Battery technology	Sealed Lead Acid (VRLA)	Package width	143 mm
Battery capacity	7 Ah	Package depth	373 mm
Battery voltage	12 V	Package height	237 mm
Battery life (max)	5 year(s)	Package weight	4.8 kg
Battery recharge time	8 h	Logistics data	
Cold start	✓	Harmonized System (HS) code	85078000



0731304344070



731304344070

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.