




Everyday™ Yellow Remanufactured Toner by Xerox compatible with Brother TN247Y, High capacity

Brand : Xerox

Product family: Everyday
Remanufactured

Product code: 006R04520

Product name : Everyday™
Yellow Remanufactured Toner
by Xerox compatible with
Brother TN247Y, High capacity



Everyday™ Yellow Remanufactured Toner by Xerox compatible with Brother TN247Y, High capacity

Everyday™ Yellow Remanufactured Toner by Xerox compatible with Brother TN247Y, High capacity:

Being environmentally responsible is simply the best way to do business, because it positively impacts the health of our planet, your company and your people. Everyday Remanufactured Toner by Xerox has the lowest carbon footprint than any single-use toner cartridge. Because you shouldn't have to choose between doing your part to reduce your eco-impact and your toner costs. And compatibility with the most popular printer brands means you can enjoy benchmark Xerox quality and stewardship no matter what kind of printer you have.

Everyday™ Yellow Remanufactured Toner by compatible with Brother TN247Y, High capacity. Colour toner page yield: 2300 pages, Black toner page yield: 2300 pages, Printing colours: Yellow, Quantity per pack: 1 pc(s)

Features		Operational conditions	
Compatibility *	DCP-L3510 DCP-L3550 HL-L3210 HL-L3230 HL-L3270 MFC-L3710 MFC-L3730 MFC-L3750 MFC-L3770	Storage temperature (T-T)	0 - 35 °C
Quantity per pack *	1 pc(s)	Storage relative humidity (H-H)	35 - 85%
Black toner page yield *	2300 pages	Weight & dimensions	
Colour toner page yield *	2300 pages	Weight	559 g
Type *	Compatible	Packaging data	
Printing colours *	Yellow	Package width	115 mm
Brand compatibility *	Brother	Package depth	345 mm
Supply type *	Single pack	Package height	85 mm
Cartridge capacity	High (XL) Yield	Package weight	690 g
OEM code	TN247Y	Package type	Box
Country of origin	Netherlands	Other features	
Operational conditions		Certification	RoHS, REACH SVHC, CE MARK STMC, ISO 9001:2015, ISO 14001:2015
Operating temperature (T-T)	17 - 25 °C	Logistics data	
Operating relative humidity (H-H)	30 - 70%	Harmonized System (HS) code	8443.99.1000
		Products per master (outer) case	6 pc(s)



0095205035407



095205035407

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date