



Lenovo 4Y41C33791 numeric keypad Universal RF Wireless Grey

Brand : Lenovo **Product code:** 4Y41C33791

Product name : 4Y41C33791

- 21-key numeric keypad
 - Industry leading scissor switch keys
 - Dedicated productivity keys (Calculator, Tab, Equal, Esc keys)
 - Minimalist design with ultra slim profile at 13 mm
 - Rechargeable , up to 3 months use in single charge (may vary based on usage)
 - Supports Lenovo Unified Pairing Receiver
- 2.4G Wireless, 21 tactile, responsive keys

Lenovo 4Y41C33791 numeric keypad Universal RF Wireless Grey:

Go beyond the limitations of your notebook and complement your workflow with a tactile, responsive 21-key keypad that sports premium scissor-switch keys and is compact enough to take on the go. With an impressive up to 3 months of battery life and a powerful 2.4 GHz wireless connector, you can rest easy knowing that your numeric keypad will be ready for action whenever you are.

Lenovo 4Y41C33791. Device interface: RF Wireless, Keyboard number of keys: 21, Purpose: Universal. Product colour: Grey. Weight: 109 g



Features		Weight & dimensions	
Key switch type	Tactile	Width	132.8 mm
Purpose *	Universal	Depth	85 mm
Device interface *	RF Wireless	Height	13.5 mm
Pointing device *	✗	Weight	109 g
USB hub *	✗	Packaging data	
Keyboard number of keys	21	Package width	180 mm
Keys operating life	10 million characters	Package depth	127 mm
Frequency band	2.4 GHz	Package height	43 mm
Design		Package weight	277 g
Ergonomic design	✓	Operational conditions	
Product colour *	Grey	Operating temperature (T-T)	0 - 40 °C
Power		Operating relative humidity (H-H)	20 - 95%
Power source type *	Battery	Other features	
System requirements		Wireless receiver interface	USB
Windows operating systems supported	✓	Logistics data	
		Harmonized System (HS) code	84716060



0195477831599



195477831599

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.