

Epson 113 EcoTank Original

Brand : Epson

Product code: C13T06B240

Product name : 113 EcoTank

113 EcoTank Pigment Cyan ink bottle, 70 ml
Epson 113 EcoTank. Type: Original, Printing colours: Cyan, Brand compatibility: Epson. Quantity per pack: 1 pc(s), Package width: 59 mm, Package depth: 175 mm. Master (outer) case length: 480 mm, Master (outer) case width: 310 mm, Master (outer) case height: 150 mm



Features		Packaging data	
Type *	Original	Package type	Box
Printing colours *	Cyan	Technical details	
Colour ink page yield	6000 pages	Master (outer) case GTIN (EAN/UPC) 8715946679839	
Colour ink volume	70 ml	Logistics data	
Ink technology	Pigment	Master (outer) case gross weight	0 g
Print technology	Inkjet	Master (outer) case length	480 mm
Brand compatibility *	Epson	Master (outer) case width	310 mm
Compatibility *	Ecotank ET-5880, EcoTank ET-5850,	Master (outer) case height	150 mm
	EcoTank ET-5800, EcoTank ET-16650, EcoTank ET-16600	Products per pallet	1350 pc(s)
Country of origin	Indonesia	Pallet gross weight	0 g
Packaging data		Products per master (outer) case	30 pc(s)
Quantity per pack *	1 pc(s)	Products per pallet (UK)	1890 pc(s)
Package width	59 mm	Pallet weight (UK)	0 g
Package depth	175 mm	Harmonized System (HS) code	84439990
Package height	58 mm		
Package weight	140 g		



8715946674711

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.