



Xerox Everyday™ Mono Drum Remanufactured by compatible with Brother DR3300, Standard capacity



Brand : Xerox

Product code: 006R04753

Product name : Everyday™ Mono Drum Remanufactured
by Xerox compatible with Brother DR3300, Standard capacity

Everyday™ Mono Drum Remanufactured by Xerox compatible with Brother DR3300, Standard capacity

Xerox Everyday™ Mono Drum Remanufactured by compatible with Brother DR3300, Standard capacity:

Being environmentally responsible is simply the best way to do business, because it positively impacts the health of our planet, your company and your people. Everyday Remanufactured Toner by Xerox has the lowest carbon footprint than any single-use toner cartridge. Because you shouldn't have to choose between doing your part to reduce your eco-impact and your toner costs. And compatibility with the most popular printer brands means you can enjoy benchmark Xerox quality and stewardship no matter what kind of printer you have.

Xerox Everyday™ Mono Drum Remanufactured by compatible with Brother DR3300, Standard capacity.
Black toner page yield: 30000 pages, Printing colours: Black, Quantity per pack: 1 pc(s)

Features		Operational conditions	
Compatibility *	DCP-8110DN HL-5440/5440D	Operating relative humidity (H-H)	30 - 70%
	HL-5440D/5440DN	Storage temperature (T-T)	0 - 35 °C
	HL-5450/5450DN/5450DNT	Storage relative humidity (H-H)	35 - 85%
	HL-5470DW/5470DWT	Weight & dimensions	
	HL-6180DW/6180DWT MFC-8710	Weight	670 g
	MFC-8950/8950DW/8950DWT	Packaging data	
Quantity per pack *	1 pc(s)	Package width	240 mm
Black toner page yield *	30000 pages	Package depth	350 mm
Type *	Compatible	Package height	155 mm
Printing colours *	Black	Package weight	1.09 kg
Brand compatibility *	Brother	Package type	Box
Supply type *	Single pack	Other features	
Cartridge capacity	Standard Yield	Certification	REACH, RoHS, WEEE, CEE ISO 9001:2015, ISO 14001:2015
Replacement for	DR-3300	Logistics data	
OEM code	DR3300	Harmonized System (HS) code	8443.91.3000
Built-in drum unit	✓	Products per master (outer) case	6 pc(s)
Country of origin	China		
Operational conditions			
Operating temperature (T-T)	17 - 25 °C		



0095205041330



095205041330



0952050413302



952050413302

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.