

ASUS ProArt PA348CGV computer monitor 86.4 cm (34") 3440 x 1440 pixels UltraWide Quad HD Black

Brand : ASUS

Product family: ProArt

Product code: 90LM07Z0-B01370

Product name : PA348CGV



- Ultra-wide 21:9 3440 x 1440 IPS 178° wide viewing angle display with a frameless design making multitasking more enjoyable and efficient
 - International color standard 98% DCI-P3 and 100% sRGB/Rec. 709 wide color gamut
 - Calman Verified with factory calibrated for excellent Delta E < 2 color accuracy
 - Extensive connectivity including DP over USB-C™ with 90W Power Delivery, DisplayPort, HDMI and USB hub
 - 120 Hz variable refresh rate (VRR) with FreeSync Premium Pro, providing creators smooth fast-rendering and comfortable viewing experience
- ASUS ProArt Display PA348CGV Professional Monitor – 34-inch, IPS, 21:9, Ultra-wide QHD (3440 x 1440), Color Accuracy ΔE < 2, Calman Verified, 98% DCI-P3, USB-C, 120Hz, FreeSync Premium Pro, Ergonomic Stand

Display		Ports & interfaces	
Display diagonal *	86.4 cm (34")	Number of USB Type-C upstream ports quantity	1
Display resolution *	3440 x 1440 pixels	USB Type-A downstream ports quantity	4
HD type *	UltraWide Quad HD	USB Power Delivery (USB PD)	✓
Native aspect ratio *	21:9	USB Power Delivery up to	90 W
Panel type *	IPS	HDMI *	✓
Backlight type	LED	HDMI ports quantity	2
Touchscreen *	✗	HDMI version	2.0
Display brightness (peak)	400 cd/m²	DisplayPorts quantity	1
Display brightness (typical)	350 cd/m²	DisplayPort version	1.4
Response time *	2 ms	Headphone out *	✓
Display surface	Matt	Headphone outputs	1
Screen shape *	Flat	Headphone connectivity	3.5 mm
Contrast ratio (typical) *	1000:1	HDCP	✓
Maximum refresh rate *	120 Hz	HDCP version	2.2
Viewing angle, horizontal	178°	Ergonomics	
Viewing angle, vertical	178°	VESA mounting *	✓
Display number of colours *	1.073 billion colours	Panel mounting interface	100 x 100 mm
Pixel pitch	0.2325 x 0.2325 mm	Cable lock slot *	✓
Pixel density	110 ppi	Cable lock slot type	Kensington
Horizontal scan range	185 - 185 kHz	Height adjustment *	✓
Vertical scan range	48 - 120 Hz	Adjustable height (max)	11.5 cm
Viewable size, horizontal	80 cm	Swivelling	✓
Viewable size, vertical	33.5 cm	Swivel angle range	30 - -30°
Digital horizontal frequency	30 - 151 kHz	Tilt adjustment	✓
Digital vertical frequency	30 - 100 Hz	Tilt angle range	23 - -5°
High Dynamic Range (HDR) supported	✓		
High Dynamic Range (HDR) technology	High Dynamic Range 10 (HDR10)		

Display		Power	
Colour gamut standard	DCI-P3	Energy efficiency class (SDR) *	G
Colour gamut	98%	Power consumption (typical) *	29.7 W
sRGB coverage (typical)	100%	Power consumption (PowerSave)	0.5 W
Performance		AC input voltage	100 - 240 V
NVIDIA G-SYNC *	✗	AC input frequency	50 - 60 Hz
AMD FreeSync *	✓	Weight & dimensions	
AMD FreeSync type	FreeSync Premium Pro	Width (with stand)	817.6 mm
Flicker-free technology	✓	Depth (with stand)	245 mm
Low Blue Light technology	✓	Height (with stand)	568.9 mm
Multimedia		Weight (with stand)	12.2 kg
Number of speakers	2	Width (without stand)	817.6 mm
RMS rated power	4 W	Depth (without stand)	68.9 mm
Built-in speaker(s) *	✓	Height (without stand)	368.2 mm
Built-in camera *	✗	Weight (without stand)	7.8 kg
Design		Packaging data	
Market positioning *	Graphics design	Package width	930 mm
Product colour *	Black	Package depth	300 mm
Feet colour	Black	Package height	488 mm
Ports & interfaces		Package weight	17 kg
Built-in USB hub *	✓	Package type	Box
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Packaging content	
USB upstream port type	USB Type-C	Cables included	DisplayPort, HDMI, USB Type-C
Number of upstream ports	1		



4711081564218



0195553557252



195553557252



4711081564225

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.