

Epson WorkForce Pro WF-7840DTWF Inkjet A4 4800 x 2400 DPI Wi-Fi

Brand : Epson

Product family: WorkForce Pro **Product code:** C11CH67401

Product name : WF-7840DTWF



- A3+ multifunction printer for business quality documents
- Wireless connectivity lets you print from anywhere
- Save money by only replacing the colour used
- Money and paper saving double-sided printing
- Enjoy hassle-free ink replacements, delivered to your door, before you run out!
- Legal Statement

A3+, Print, Scan, Copy, Fax, 4800 x 2400 DPI, USB, LAN, WLAN, Touchscreen, 20.6 kg

Epson WorkForce Pro WF-7840DTWF. Print technology: Inkjet, Printing: Colour printing, Maximum resolution: 4800 x 2400 DPI. Scanning: Colour scanning, Optical scanning resolution: 1200 x 2400 DPI. Faxing: Colour faxing. Duplex functions: Print. Maximum ISO A-series paper size: A4. Wi-Fi. Product colour: Black

Printing		Input & output capacity	
Print technology *	Inkjet	Total number of input trays *	3
Printing *	Colour printing	Total output capacity *	125 sheets
Duplex printing *	✓	Auto document feeder (ADF)	✓
Maximum resolution *	4800 x 2400 DPI	Paper handling	
Print speed (ISO/IEC 24734) mono	25 ipm	Maximum ISO A-series paper size *	A4
Print speed (ISO/IEC 24734) colour	12 ipm	Paper tray media types *	Plain paper
Duplex print speed (black, normal quality, A4/US Letter)	16 ppm	ISO A-series sizes (A0...A9) *	A3, A3+, A4, A5, A6
Duplex print speed (colour, normal quality, A4/US Letter)	9 ppm	ISO B-series sizes (B0...B9)	B5
Copying		Non-ISO print media sizes	Legal, Letter
Duplex copying *	✗	Envelopes sizes	10, C4, C6, DL
Copying *	✗	Photo paper sizes	9x13,10x15,13x18
Scanning		Paper tray media weight	64 - 256 g/m ²
Scanning *	Colour scanning	Ports & interfaces	
Optical scanning resolution *	1200 x 2400 DPI	USB port	✓
Scan technology	CIS	Network	
Scan to	Cloud	Wi-Fi *	✓
Image formats supported	BMP, JPEG, PNG, TIFF	Ethernet LAN *	✓
Document formats supported	PDF	Security algorithms	64-bit WEP, 128-bit WEP, WPA-PSK, SNMP, HTTP, DHCP, BOOTP, APIPA, DDNS, mDNS, SNTP, SLP, WSD, LLTD, Ping
Fax		Management protocols	
Faxing *	Colour faxing	Mobile printing technologies	Apple AirPrint, Epson Connect
Fax transmission speed	3 sec/page	Performance	
Modem speed	33.6 Kbit/s	Card reader integrated	✗
Fax memory	550 pages	Design	
Auto-redialing	✓	Product colour *	Black
Speed dialling	✓	Market positioning *	Home & office
Error Correction Mode (ECM)	✓	Built-in display *	✓
Features		Colour display	✓
Maximum duty cycle *	50000 pages per month	Weight & dimensions	
Duplex functions *	Print	Width	515 mm
Number of print cartridges *	4	Depth	450 mm
Printing colours *	Black, Cyan, Magenta, Yellow	Height	350 mm
Page description languages	ESC/P-R	Weight	20.6 kg

Packaging content	
-------------------	--

Cartridge(s) included	✓
-----------------------	---

Logistics data	
----------------	--

Harmonized System (HS) code	84433100
-----------------------------	----------



8715946668383

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.