



Everyday™ Yellow Remanufactured Toner by Xerox compatible with Samsung CLT-Y506L, High capacity

Brand : Xerox

Product family: Everyday

Product code: 006R04315

Product name : Everyday™
Yellow Remanufactured Toner by
Xerox compatible with Samsung
CLT-Y506L, High capacity




Everyday™ Yellow Remanufactured Toner by Xerox compatible with Samsung CLT-Y506L, High capacity

Everyday™ Yellow Remanufactured Toner by Xerox compatible with Samsung CLT-Y506L, High capacity:

Being environmentally responsible is simply the best way to do business, because it positively impacts the health of our planet, your company and your people. Everyday Remanufactured Toner by Xerox has the lowest carbon footprint than any single-use toner cartridge. Because you shouldn't have to choose between doing your part to reduce your eco-impact and your toner costs. And compatibility with the most popular printer brands means you can enjoy benchmark Xerox quality and stewardship no matter what kind of printer you have.

Everyday™ Yellow Remanufactured Toner by compatible with Samsung CLT-Y506L, High capacity. Black toner page yield: 3500 pages, Colour toner page yield: 3500 pages, Printing colours: Yellow, Quantity per pack: 1 pc(s)



Features

Compatibility *	CLP-680 CLX-6260
Quantity per pack *	1 pc(s)
Colour toner cartridges quantity	1
Black toner page yield *	3500 pages
Colour toner page yield *	3500 pages
Type *	Compatible
Printing colours *	Yellow
Brand compatibility *	Samsung
Supply type *	Single pack
Cartridge capacity	High (XL) Yield
OEM code	CLT-Y506L

Features

Country of origin	China
-------------------	-------

Packaging data

Package width	135 mm
Package depth	350 mm
Package height	105 mm
Package weight	1.07 kg
Package type	Box

Other features

Print technology	Laser printing
------------------	----------------

Logistics data

Export Control Classification Number (ECCN)	EAR99
Harmonized System (HS) code	84439990



0095205067736



095205067736

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date