



Canon CLI-551 BK/C/M/Y Ink Cartridge Multipack

Brand : CanonProduct code: 6509B009

Product name : CLI-551 BK/C/M/Y Ink Cartridge Multipack

- Genuine Canon Ink produces on average 35% more quality prints than imitation cartridges***
 - Genuine Canon Ink provides consistent quality prints 100% of the time***
 - Genuine Canon Ink is 100% reliable so you can print with less stress***
 - Return every toner ink and toner cartridge to be reused or recycled. It's free, easy and environmentally friendly.
- CLI-551 BK/C/M/Y Ink Cartridge Multipack

Canon CLI-551 BK/C/M/Y Ink Cartridge Multipack:

This multipack contains one each of cyan, magenta, yellow and black ink tanks. The set of four 7ml ink tanks offer you convenience and savings. The ChromaLife100+ system combined with Canon photo papers delivers stunning results and longevity.
Canon CLI-551 BK/C/M/Y Ink Cartridge Multipack. Cartridge capacity: Standard Yield, Supply type: Multi pack, Printing colours: Black, Cyan, Magenta, Yellow, Quantity per pack: 4 pc(s)

Features		Operational conditions	
Print technology	Inkjet printing	Operating relative humidity (H-H)	5 - 95%
Compatibility *	PIXMA iP7250, PIXMA iP8750, PIXMA iX6850, PIXMA MG5450, PIXMA MG5550, PIXMA MG5650, PIXMA MG6350, PIXMA MG6450, PIXMA MG6650, PIXMA MG7150, PIXMA MG7550, PIXMA MX725, PIXMA MX925	Storage temperature (T-T)	10 - 35 °C
		Operating temperature (T-T)	15 - 35 °C
		Storage relative humidity (H-H)	5 - 95%
		Packaging data	
		Package width	151 mm
Quantity per pack *	4 pc(s)	Package depth	117 mm
Type *	Original	Package height	52 mm
Cartridge capacity	Standard Yield	Package weight	119 g
Ink type	Pigment-based ink	Package type	Blister
Printing colours *	Black, Cyan, Magenta, Yellow	Other features	
Brand compatibility *	Canon	Page yield footnote	ISO/IEC 24734
Supply type *	Multi pack	Logistics data	
OEM code	CLI-551 C/M/Y/BK MULTI BL	Harmonized System (HS) code	84439990
Country of origin	Japan		
Colour	✓		





8714574584416

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.