

Brother TN-3380TWIN toner cartridge 2 pc(s) Original Black

Brand : Brother

Product code: TN-3380TWIN

Product name : TN-3380TWIN



- Each cartridge prints 8,000 pages in accordance with ISO/IEC19752
 - High quality genuine Brother cartridges
 - Prevents waste to save you paper, time and money
- The Brother TN-3380TWIN Black Toner Cartridge Twin Pack. Each cartridge prints 8,000 pages.

Brother TN-3380TWIN toner cartridge 2 pc(s) Original Black:

Designed to last much longer than a standard cartridge, the high yield ink refill cartridges in this genuine TN-3380TWIN Twin Pack go further without any loss of quality. Buy this TN-3380TWIN Twin Pack and you can replenish your toner and also have a replacement cartridge on hand for next time.
Brother TN-3380TWIN. Black toner page yield: 16000 pages, Printing colours: Black, Quantity per pack: 2 pc(s)

Features		Packaging data	
Compatibility *	HL-5440D, HL-5450DN, HL-5470DW, HL-6180DW	Package weight	2.01 kg
Quantity per pack *	2 pc(s)	Package type	Box
Black toner page yield *	16000 pages	Other features	
Type *	Original	Print technology	Laser printing
Printing colours *	Black	Logistics data	
Brand compatibility *	Brother	Harmonized System (HS) code	84439990
Cartridge return & recycling	✓	Master (outer) cases per pallet layer	8 pc(s)
Product colour	Black	Master (outer) cases per pallet	56 pc(s)
Country of origin	China	Layers per pallet	7 pc(s)
Weight & dimensions		Products per pallet	56 pc(s)
Width	293 mm	Pallet gross height	15.8 cm
Depth	205 mm	Pallet gross weight	118.8 kg
Height	363 mm	Pallet type	800 x 1200 mm
Weight	1.4 kg		



4977766709811

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.