



APC NetShelter Cable Management, Vertical Cable Manager, for NetShelter SX 750mm Wide 48U, 97 x 2184 x 160 mm



Brand : APCProduct code: AR7588

Product name : APC NetShelter Cable Management, Vertical Cable Manager, for NetShelter SX 750mm Wide 48U, 97 x 2184 x 160 mm

APC NetShelter Cable Management, Vertical Cable Manager, for NetShelter SX 750mm Wide 48U, 97 x 2184 x 160 mm


APC NetShelter Cable Management, Vertical Cable Manager, for NetShelter SX 750mm Wide 48U, 97 x 2184 x 160 mm:

The vertical channels AR7588 have smooth plastic fingers at 1U increments to allow patch cords to enter and exit in an organized manner. This vertical cable manager for the NetShelter SX series 48U and 750mm Wide provides maximum U-space coverage. It supports 190 to 250 CAT 6A/CAT 6 data cables per section and 190 CAT 6A per channel section. Easily secure and access cabling with toolless mounting on the backplate for accessories and snap hinge cable retainers. The vertical channels have smooth plastic fingers at 1U increments to allow patch cords to enter and exit in an organized manner. Each kit covers one corner of the enclosure and includes mounting hardware, 6x cable retainers with snap APC NetShelter Cable Management, Vertical Cable Manager, for NetShelter SX 750mm Wide 48U, 97 x 2184 x 160 mm. Type: Straight cable tray, Form factor: Vertical, Product colour: Black

Features		Technical details	
Type *	Straight cable tray	Total carbon footprint (kg of CO2e)	17.39
Form factor	Vertical	Logistics data	
Product colour	Black	Harmonized System (HS) code	85389099
Certification	RoHS		



0731304301004



731304301004

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.