



BenQ MS560 Standard throw projector 4000 ANSI lumens DLP SVGA (800x600) White

Brand : BenQ

Product code: 9H.JND77.13E

Product name : MS560



- 4000 ANSI Lumen High brightness and 20,000:1 High Contrast
 - Exclusive Data Review Mode Showcases Text and Charts in Detail
 - SmartEco Mode Saves Lamp Power Up To 70%
- DLP, 4000 lm, 1920 x 1200, 34 /29 dBA, 2xHDMI, USB Type-A, USB Mini-B, D-SUB, RS-232, 296 x 120 x 221 mm, 2.3kg

BenQ MS560. Projector brightness: 4000 ANSI lumens, Projection technology: DLP, Projector native resolution: SVGA (800x600). Light source type: Lamp, Service life of light source: 6000 h, Service life of light source (economic mode): 10000 h. Zoom ratio: 1.1:1, Throw ratio: 1.96 - 2.15, Offset: 110%. Analog signal format system: NTSC, PAL, SECAM, Supported graphics resolutions: 640 x 480 (VGA), 1920 x 1200 (WUXGA), Supported video modes: 480i, 480p, 576i, 576p, 720p, 1080i, 1080p. Serial interface type: RS-232, HDMI connector type: Full-size



Projector		Storage	
Supported aspect ratios	4:3	Card reader integrated *	✗
Screen size compatibility *	1524 - 3810 mm (60 - 150")	Features	
Projector brightness *	4000 ANSI lumens	Noise level (economic mode)	29 dB
Projection technology *	DLP	On Screen Display (OSD)	✓
Projector native resolution *	SVGA (800x600)	On Screen Display (OSD) languages	Arabic, Bulgarian, Simplified Chinese, Traditional Chinese, Croatian, Czech, Danish, German, Dutch, English, Spanish, Farsi, Finnish, French, Greek, Hindi, Hungarian, Indonesian, Italian, Japanese, Korean, Norwegian, Polish, Portuguese, Romanian, Russian, Swedish, Thai, Turkish, Vietnamese
Contrast ratio (typical) *	20000:1		
Native aspect ratio *	4:3		
Number of colours	1.073 billion colours		
Horizontal scan range	15 - 102 kHz	Number of OSD languages	30
Vertical scan range	23 - 120 Hz	Noise level *	34 dB
Keystone correction, vertical	-40 - 40°	Air filter	✓
Light source		Multimedia	
Light source type *	Lamp	Built-in speaker(s) *	✓
Service life of light source *	6000 h	RMS rated power	10 W
Service life of light source (economic mode)	10000 h	Number of built-in speakers	1
Lens system		Design	
Zoom ratio	1.1:1	Market positioning *	Business
Throw ratio	1.96 - 2.15	Product type *	Standard throw projector
Offset	110%	Product colour *	White
Video		Placement	Ceiling
Analog signal format system *	NTSC, PAL, SECAM	Cable lock slot	✓
Full HD *	✓	Cable lock slot type	Kensington
Supported graphics resolutions	640 x 480 (VGA), 1920 x 1200 (WUXGA)		
Supported video modes	480i, 480p, 576i, 576p, 720p, 1080i, 1080p		

Ports & interfaces		Display	
HDMI connector type	Full-size	Built-in display *	✗
S-Video inputs quantity	1	Power	
USB 2.0 ports quantity	1	Power source *	AC
Mini-USB 2.0 ports quantity	1	Power consumption (typical) *	260 W
Serial interface type *	RS-232	Power consumption (standby) *	0.5 W
PC Audio in	✓	Power consumption (max)	280 W
PC Audio out	✓	Power consumption (economy mode)	215 W
PC in (D-Sub)	✓	AC input voltage	100 - 240 V
VGA (D-Sub) ports quantity *	1	AC input frequency	50 - 60 Hz
HDMI ports quantity *	2	Operational conditions	
Composite video in *	1	Operating temperature (T-T)	0 - 40 °C
DVI port *	✗	Weight & dimensions	
Network		Width	296 mm
Smart TV *	✗	Depth	221 mm
Ethernet LAN *	✗	Height	120 mm
Wi-Fi *	✗	Weight *	2.3 kg
		Packaging content	
		Remote control included *	✓
		Remote control type	IR
		Batteries included	✓
		Cables included	AC, VGA
		Logistics data	
		Quantity per pack	1 pc(s)
		Harmonized System (HS) code	85286200



4718755084195

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.