



APC 3.5kW split system Indoor unit, Gravity Drain

Brand : APC

Product code: ACRMD4KI-1

Product name : 3.5kW split system Indoor unit, Gravity Drain




- Powerfully Compact- precise temperature control to cool most single racks with zero need for alternative solutions
 - Enhanced Flexibility-Installs and integrates quickly and simply at the bottom of the IT Rack
 - Variable Capacity- continuous and automatic modulation of fan and compressor speed to match rack airflow requirements
 - Robust Design- for 24/7 continuous operation and convenient servicing of critical components outside the IT space
- 3.5kW split system Indoor unit, Gravity Drain

APC 3.5kW split system Indoor unit, Gravity Drain:

This product ACRMD4KI-1 is a Compact, intelligent cooling for your Edge Data Center.
APC 3.5kW split system Indoor unit, Gravity Drain. Type: Air conditioner indoor unit, Product colour: Black, Air conditioner functions: Circulation, Cooling, Heating. Design load (cooling): 3.5 kW, Design load (heating) (Warmer heating season): 3.5 kW, Design load (heating) (Average heating season): 3.5 kW. Indoor unit noise level (high speed): 62.5 dB, Indoor unit width: 47.4 cm, Indoor unit depth: 75.2 cm



Features		Power	
Type *	Air conditioner indoor unit	Design load (heating) (Average heating season) *	3.5 kW
Multi-split *	✗	Design load (heating) (Colder heating season)	3.5 kW
Product colour *	Black	Network	
Air conditioner functions *	Circulation, Cooling, Heating	Wi-Fi *	✗
Inverter technology *	✗	Indoor unit	
Auto fan	✓	Indoor unit noise level (high speed)	62.5 dB
Compressor type	Rotary	Indoor unit width	47.4 cm
Air filter	✓	Indoor unit depth	75.2 cm
Power		Indoor unit height	21.8 cm
Design load (cooling) *	3.5 kW	Indoor unit weight	26 kg
Design load (heating) (Warmer heating season) *	3.5 kW		



0731304403746



731304403746

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.