

ASUS ProArt PA278QV computer monitor 68.6 cm (27") 2560 x 1440 pixels Quad HD LED Black

Brand : ASUS

Product family: ProArt

Product code: 90LM05L1-B03370

Product name : PA278QV

- 27-inch WQHD (2560x 1440) IPS monitor with frameless design
- International color standard 100% sRGB and 100% Rec. 709 wide color gamut
- Calman Verified with factory calibrated for excellent Delta E < 2 color accuracy
- ASUS-exclusive ProArt Preset and ProArt Palette provide numerous adjustable color parameters
- Extensive connectivity for maximum flexibility, including Mini DisplayPort, DisplayPort, HDMI, dual-link DVI-D, audio in and earphone jack, plus four USB 3.0 ports
- Ergonomic stand with tilt, swivel, pivot and height adjustments for a comfortable viewing experience, plus VESA wall-mountable
- 27", 16:9, 2560x1440, IPS, RMS 2x 2W, HDMI, DL DVI-D, DP, 3.5mm, 4x USB 3.0, 615x382-532x226 mm, black



Display		Ports & interfaces	
Display diagonal *	68.6 cm (27")	Audio input	✓
Display resolution *	2560 x 1440 pixels	Headphone out *	✓
HD type *	Quad HD	Headphone outputs	1
Native aspect ratio *	16:9	Headphone connectivity	3.5 mm
Display technology *	LED	HDCP	✓
Panel type *	IPS	Ergonomics	
Touchscreen *	✗	VESA mounting *	✓
Display brightness (typical)	350 cd/m²	Panel mounting interface	100 x 100 mm
Response time *	5 ms	Cable lock slot *	✓
Display surface	Matt	Cable lock slot type	Kensington
Screen shape *	Flat	Height adjustment *	✓
Supported graphics resolutions	640 x 480 (VGA), 720 x 400, 720 x 480, 720 x 576, 800 x 600 (SVGA), 1024 x 768 (XGA), 1152 x 864 (XGA+), 1280 x 1024 (SXGA), 1280 x 720 (HD 720), 1280 x 768 (WXGA), 1280 x 800 (WXGA), 1280 x 960, 1440 x 900 (WXGA+), 1680 x 1050 (WSXGA+), 1920 x 1080 (HD 1080), 1920 x 1200 (WUXGA)	Adjustable height (max)	15 cm
		Pivot	✓
		Pivot angle	-90 - 90°
Supported video modes	480p, 576p, 720p, 1080p	Swivelling	✓
Contrast ratio (typical) *	1000:1	Swivel angle range	-90 - 90°
Contrast ratio (dynamic)	100000000:1	Tilt adjustment	✓
Dynamic contrast ratio marketing name	SmartContrast	Tilt angle range	-5 - 35°
Maximum refresh rate *	75 Hz	On Screen Display (OSD)	✓
Viewing angle, horizontal	178°	On Screen Display (OSD) languages	Simplified Chinese, Traditional Chinese, Croatian, Czech, German, Dutch, English, Spanish, French, Hungarian, Indonesian, Italian, Japanese, Korean, Polish, Portuguese, Romanian, Russian, Thai, Turkish
Viewing angle, vertical	178°		
Display number of colours *	16.78 million colours		
Pixel pitch	0.2331 x 0.2331 mm	Number of OSD languages	21
Viewable size, horizontal	59.7 cm	LED indicators	✓
Viewable size, vertical	33.6 cm	Power	
Viewable size diagonal	68.5 cm	Energy efficiency class (SDR) *	G
Digital horizontal frequency	30 - 112 kHz	Energy consumption (SDR) per 1000 hours *	32 kWh
Digital vertical frequency	46 - 75 Hz	Power consumption (typical) *	32.1 W
Colour gamut standard	sRGB		

Display		Power	
sRGB coverage (typical)	100%	Power consumption (standby) *	0.5 W
Performance		Power consumption (off)	0.3 W
NVIDIA G-SYNC *	✗	AC input voltage	100 - 240 V
AMD FreeSync *	✗	Energy efficiency scale	A to G
VESA Adaptive Sync support	✓	Operational conditions	
Flicker-free technology	✓	Operating temperature (T-T)	0 - 40 °C
Low Blue Light technology	✓	Storage temperature (T-T)	-20 - 60 °C
Multimedia		Weight & dimensions	
Number of speakers	2	Width (with stand)	615 mm
RMS rated power	4 W	Depth (with stand)	226 mm
Built-in speaker(s) *	✓	Height (with stand)	532 mm
Built-in camera *	✗	Weight (with stand)	7.72 kg
Design		Width (without stand)	615 mm
Market positioning *	Graphics design	Depth (without stand)	51 mm
Product colour *	Black	Height (without stand)	372 mm
Frameless design	✓	Weight (without stand)	4.96 kg
Feet colour	Black	Packaging data	
Ports & interfaces		Package width	735 mm
Built-in USB hub *	✓	Package depth	216 mm
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Package height	464 mm
Number of upstream ports	1	Package weight	10.8 kg
USB Type-A downstream ports quantity	4	Packaging content	
DVI port	✓	Stand included	✓
DVI-D ports quantity	1	Cables included	AC
HDMI *	✓	Other features	
HDMI ports quantity	1	Certification	Energy Star, BSMI, CB, CCC, CEL level , CU, ErP, FCC, ISO-9241-307, J-MOSS, KCC, PSE, TUV-Ergo, TUV-GS, UkrSEPRO, UL/cUL, VCCI, WEEE, WHQL (Windows 10, Windows 7), RCM, TUV Flicker-free , KC , eStandby, TUV Low Blue Light, TCO, ICES-3, PC recycle
HDMI version	1.4		
DisplayPorts quantity	1		
DisplayPort version	1.2		
Mini DisplayPorts quantity	1		
		Logistics data	
		Harmonized System (HS) code	85285210



4718017603614

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.