

Targus AMB581GL mouse Ambidextrous RF Wireless + Bluetooth

Brand : Targus
Product code: AMB581GL
Product name : AMB581GL

Wireless, Bluetooth, MacOS and Windows, Tablet/Phone Device

Targus AMB581GL mouse Ambidextrous RF Wireless + Bluetooth:

Put productivity at your fingertips with the Compact Multi-Device Dual Mode Antimicrobial Wireless Mouse. Experience freedom from cords with two wireless connectivity options, 2.4 GHz or Bluetooth. Sporting a simple, pebble-shaped design, easily click, point, and scroll using the three essential buttons you need.

For an added benefit, this mouse features Targus DefenseGuard Antimicrobial Protection, which creates a cleaner surface and works continuously to protect the mouse by preventing the growth of microorganisms. Unlike topically applied sprays, DefenseGuard mice are treated with an antimicrobial additive that does not wear off and lasts for the life of the product.
Targus AMB581GL. Form factor: Ambidextrous. Device interface: RF Wireless + Bluetooth, Buttons type: Pressed buttons, Buttons quantity: 1, Scroll type: Ring. Power source: Batteries. Product colour: Black



Mouse		Power	
Number of scroll wheels	1	Power source *	Batteries
Scrolling directions	Vertical	System requirements	
Device interface *	RF Wireless + Bluetooth	Windows operating systems supported	✓
Buttons type	Pressed buttons	Mac operating systems supported	✓
Scroll type *	Ring	Weight & dimensions	
Buttons quantity *	1	Width	60.5 mm
Multi-device support	✓	Depth	109.2 mm
Frequency band	2.4 GHz	Height	31 mm
Bluetooth version	5.0	Weight	58.97 g
Design		Packaging data	
Form factor *	Ambidextrous	Quantity per pack *	1 pc(s)
Product colour *	Black	Package type	Box
Surface coloration	Monochromatic	Logistics data	
Illumination	✗	Harmonized System (HS) code	84716070



0092636353056



092636353056



5051794034523



4070071967072

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.