




Lenovo 4X67A81547 graphics card NVIDIA A2 16 GB GDDR6

Brand : Lenovo

Product code: 4X67A81547

Product name : 4X67A81547



ThinkSystem NVIDIA A2 16GB PCIe Gen4 Passive GPU

Lenovo 4X67A81547 graphics card NVIDIA A2 16 GB GDDR6:

The NVIDIA A2 Tensor Core GPU provides entry-level inference with low power, a small footprint, and high performance for NVIDIA AI at the edge. Featuring a low-profile PCIe Gen4 card and a low 40-60W configurable thermal design power (TDP) capability, the A2 brings versatile inference acceleration to any server for deployment at scale.

Lenovo 4X67A81547. Graphics processor family: NVIDIA, Graphics processor: A2. Discrete graphics card memory: 16 GB, Graphics card memory type: GDDR6. Interface type: PCI Express x8 4.0. Cooling type: Passive

Processor		Ports & interfaces	
CUDA *	✓	Interface type *	PCI Express x8 4.0
Graphics processor family *	NVIDIA	Design	
Graphics processor *	A2	Cooling type *	Passive
Memory		Bracket height	Low-Profile (LP)
Discrete graphics card memory *	16 GB	Number of slots	1
Graphics card memory type *	GDDR6	Power	
Memory bandwidth (max)	200 GB/s	Minimum system power supply *	40 W
		Power consumption (typical) *	60 W



0889488628162



889488628162

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.