



TP-Link DeltaStream 4-port Pizza-box GPON Optical Line Terminal

Brand : TP-Link

Product family: DeltaStream

Product code: DS-P7001-04

Product name : DeltaStream 4-port Pizza-box GPON Optical Line Terminal



4× 2.5G PON, 1× 10 Gbps SFP+ Uplink, 1× 10/100/1000 Mbps RJ45 Uplink, 1× RJ45 Console, 1× RJ45 MGMT, 1× Alarm Port, 440 × 180 × 44 mm

TP-Link DeltaStream 4-port Pizza-box GPON Optical Line Terminal:

4-Port GPON Optical Line Terminal

4 GPON Ports, Supports 512 ONUs

Supports 1:128 splitting ratio for every port—up to 512 ONTs by one device.



Free Centralized Management Via DeltaStream PON Management System (DPMS)

Easy maintenance and centralized management makes your life a breeze. Configure and update all your devices at once via DeltaStream PON Management System (DPMS), SNMP, CLI and Web UI.

- No Additional Expense
- Improve Management Efficiency And Reduce Maintenance Costs
- The Easy-to-Use Dashboard Ensures Hassle-Free Configuration

Compact Size, Flexible Deployment

Mount in a rack for flexible deployment with all your other products.

Constant Reliability Through Redundant Dual Power Supplies

Dual built-in AC and DC power supplies ensures carrier-class reliability.


Features		Ports & interfaces	
Static route	✓	SFP/SFP+ slots quantity	1
DHCP server	✓	Power	
DHCP relay	✓	AC input voltage	100 - 240 V
IGMP snooping	✓	AC input frequency	50 - 60 Hz
Multicast Listener Discovery (MLD) snooping	✓	DC voltage range	38.4 - 72 V
Quality of Service (QoS) support	✓	Power consumption (max)	58 W
GPON split ratio (max)	1:128	Operational conditions	
Maximum operating distance (GPON)	20000 m	Operating temperature (T-T)	0 - 50 °C
Access Control List (ACL)	✓	Storage temperature (T-T)	-40 - 70 °C
Ports & interfaces		Operating relative humidity (H-H)	10 - 90%
Upstream ports	Gigabit Ethernet	Storage relative humidity (H-H)	5 - 90%
Ethernet LAN (RJ-45) ports	2	Weight & dimensions	
GPON ports quantity	4	Width	440 mm
		Depth	180 mm
		Height	44 mm



4897098683163



4897098683156



0840030703164



840030703164

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.