



D-Link Wireless AC1200 Wave2 Dual-Band Industrial Access Point

Brand : D-Link

Product code: DIS-2650AP

Product name : D-Link Wireless AC1200 Wave2 Dual-Band Industrial Access Point

- Superior speeds and throughput with dual-band 802.11ac Wave 2 Wi-Fi, offering speeds of up to 1200 Mbps
 - 2x2 MU-MIMO better handles multiple devices & sensors and enhances capacity
 - Two 10/100/1000BASE-T Ethernet ports (one supports PoE 802.11at)
 - Airtime Fairness, Band Steering and Fast Roaming greatly optimize connectivity for all devices
 - Supports WPA2 Encryption security for more protection
 - Easy to manage with D-Link's free software-based management solution, Nuclias Connect
 - Broad temperature tolerance of -20 to 65°C
 - DIN rail or wall mountable
 - Built-in 2KV surge protection and 15KV ESD protection
 - Dual power input for redundant power supplies
- IEEE 802.11a/b/g/n/ac, 2.4/5 GHz, 2x 1G LAN, 196.2x105.9x40 mm



Features		Antenna	
2.4 GHz *	✓	Antenna type *	External
5 GHz *	✓	Antenna direction type	Omni-directional
Maximum data transfer rate *	1200 Mbit/s	Antennas quantity	2
Maximum data transfer rate (2.4 GHz)	300 Mbit/s	Antenna gain level (max)	3 dBi
Maximum data transfer rate (5 GHz)	866 Mbit/s	Certificates	
Ethernet LAN data rates	10,100,1000 Mbit/s	Certification	FCC, CE, LVD
Networking standards	IEEE 802.11a, IEEE 802.11ac, IEEE 802.11b, IEEE 802.11g, IEEE 802.11n, IEEE 802.3ab, IEEE 802.3at, IEEE 802.3az, IEEE 802.3u	Weight & dimensions	
Security		Width	196.2 mm
Security algorithms *	64-bit WEP, 128-bit WEP, SSID, SSL/TLS, WPA, WPA2	Depth	105.9 mm
Management features		Height	40 mm
Web-based management	✓	Weight	785 g
Ports & interfaces		Packaging content	
Ethernet LAN (RJ-45) ports *	2	Quantity per pack	1 pc(s)
Power		Operational conditions	
Power over Ethernet (PoE) *	✓	Operating relative humidity (H-H)	10 - 90%
Power consumption (max)	14.478 W	Operating temperature (T-T)	-20 - 65 °C
Design		Storage temperature (T-T)	-40 - 80 °C
Placement *	Wall	Storage relative humidity (H-H)	5 - 95%
Product colour *	Black	Logistics data	
		Harmonized System (HS) code	85176990



0790069458675



790069458675

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.