

Brother TN-247BKTWIN toner cartridge 2 pc(s) Original Black

Brand : Brother

Product code: TN-247BKTWIN

Product name : TN-247BKTWIN

Genuine Brother TN247BKTWIN black toner cartridge twin pack. Each cartridge prints up to 3,000 pages.

Brother TN-247BKTWIN toner cartridge 2 pc(s) Original Black:

Designed specifically for your printer, the genuine Brother TN247BKTWIN high yield toner value pack, gives you two black toner cartridges in one handy pack, each printing up to 3,000 pages. Compatible with a range of printers, our easy to install cartridges will help you produce long-lasting documents that won't smudge or fade over time. Brother consider the environmental impact at every stage of your laser toner life cycle, reducing waste at landfill. All our hardware and toner cartridges are built to have as little impact on the environment as possible. Genuine Brother TN247BKTWIN laser toner cartridges – worth it every time.

Brother TN-247BKTWIN. Black toner page yield: 3000 pages, Printing colours: Black, Quantity per pack: 2 pc(s)



Features		Weight & dimensions	
Compatibility *	HL-L3230CDW/L3270CDW, DCP-L3550CDW, MFC-L3730CDN/L3750CDW/L3770CDW	Height	205 mm
Quantity per pack *	2 pc(s)	Weight	847 g
Black toner cartridges quantity	2	Packaging data	
Black toner page yield *	3000 pages	Package weight	1.64 kg
Type *	Original	Logistics data	
Printing colours *	Black	Harmonized System (HS) code	84439990
Brand compatibility *	Brother	Master (outer) cases per pallet layer	6 pc(s)
Supply type *	Twin pack	Master (outer) cases per pallet	54 pc(s)
Country of origin	Vietnam	Layers per pallet	9 pc(s)
Weight & dimensions		Products per pallet	108 pc(s)
Width	385 mm	Pallet gross height	17.2 cm
Depth	155 mm	Pallet gross weight	197.3 kg
		Pallet type	1200 x 1000 mm



4977766812726



5715328104457

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.