



Lenovo 4XC1D51447 network card Internal WWAN 600 Mbit/s

Brand : Lenovo

Product code: 4XC1D51447

Product name : 4XC1D51447



- Size: 42*30*2.3mm
 - Weight: approx. 6.8 g
 - PCI Express M.2 Interface
 - Main and Rx-diversity/GNSS antenna connectors
 - 2 x 2 MIMO in DL direction
 - Data rate: up to 600 Mbps (Downlink)/150 Mbps (Uplink)
- ThinkPad Quetcel SDX24 EM120R-GL CAT12 PCIE WWAN Module

Lenovo 4XC1D51447 network card Internal WWAN 600 Mbit/s:

ThinkPad Quetcel SDX24 EM120R-GL CAT12 WWAN Module I is a wireless communication module with receive diversity. It helps provide data connectivity and network with standard PCI Express M.2 interface. With downlink speed of up to 600 Mbps and uplink speed of up to 150 Mbps, the CAT12 WWAN module enhances the network reliability and availability of your ThinkPad, and provides a great cellular solution for travelers to sustain mobility while using PC devices.

Lenovo 4XC1D51447. Internal. Connectivity technology: Wired, Host interface: M.2, Interface: WWAN. Maximum data transfer rate: 600 Mbit/s

Ports & interfaces		Operational conditions	
Connectivity technology *	Wired	Operating relative humidity (H-H)	5 - 95%
Host interface *	M.2	Weight & dimensions	
Interface *	WWAN	Width	42 mm
Network		Depth	30 mm
Maximum data transfer rate *	600 Mbit/s	Height	2.3 mm
Design		Weight	6.8 g
Component for *	Laptop	Packaging data	
Internal *	✓	Package width	53 mm
Certification	CE,FCC,ANATEL,TELEC&JATE,RCM	Package depth	144 mm
	SDoC,KC,NCC,IC, ICASA, IFETEL	Package height	177 mm
Operational conditions		Package weight	70 g
Operating temperature (T-T)	-25 - 75 °C	Logistics data	
		Harmonized System (HS) code	85176990



0195892020929



195892020929

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.