



Everyday™ Black Toner by Xerox compatible with Samsung MLT-D101S, Standard capacity

Brand : Xerox Product family: Everyday Product code: 006R04293

Product name : Everyday™
Black Toner by Xerox compatible
with Samsung MLT-D101S,
Standard capacity

Everyday™ Black Toner by Xerox compatible with Samsung MLT-D101S, Standard capacity

Everyday™ Black Toner by Xerox compatible with Samsung MLT-D101S, Standard capacity:

Being environmentally responsible is simply the best way to do business, because it positively impacts the health of our planet, your company and your people. Everyday Remanufactured Toner by Xerox has the lowest carbon footprint than any single-use toner cartridge. Because you shouldn't have to choose between doing your part to reduce your eco-impact and your toner costs. And compatibility with the most popular printer brands means you can enjoy benchmark Xerox quality and stewardship no matter what kind of printer you have.

Everyday™ Black Toner by compatible with Samsung MLT-D101S, Standard capacity. Black toner page yield: 1500 pages, Printing colours: Black, Quantity per pack: 1 pc(s)



Everyday™
Toner
by Xerox

Cut Toner Costs, Not Quality

Save big with 40-60% savings on major printer brands.

Features		Packaging data	
Compatibility *	ML-2160 ML-2165 SF-760 MFP	Package width	115 mm
Quantity per pack *	1 pc(s)	Package depth	325 mm
Black toner cartridges quantity	1	Package height	115 mm
Black toner page yield *	1500 pages	Package weight	740 g
Type *	Compatible	Package type	Box
Printing colours *	Black	Other features	
Brand compatibility *	Samsung	Print technology	Laser printing
Supply type *	Single pack	Logistics data	
Cartridge capacity	Standard Yield	Export Control Classification Number (ECCN)	EAR99
OEM code	MLT-D101S	Harmonized System (HS) code	84439990
Country of origin	China		



0095205067514



095205067514

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date