


StarTech.com 100 Adhesive Cable Management Clips Black - Network/Ethernet/Office Desk/Computer Cord Organizer - Sticky Cable/Wire Holders - Nylon Self Adhesive Clamp UL/94V-2 Fire Rated

Brand : StarTech.com

Product code: CBMCC3

Product name : 100 Adhesive Cable Management Clips Black - Network/Ethernet/Office Desk/Computer Cord Organizer - Sticky Cable/Wire Holders - Nylon Self Adhesive Clamp UL/94V-2 Fire Rated

StarTech.com 100 Adhesive Cable Management Clips Black - Network/Ethernet/Office Desk/Computer Cord Organizer - Sticky Cable/Wire Holders - Nylon Self Adhesive Clamp UL/94V-2 Fire Rated (CBMCC3) StarTech.com 100 Adhesive Cable Management Clips Black - Network/Ethernet/Office Desk/Computer Cord Organizer - Sticky Cable/Wire Holders - Nylon Self Adhesive Clamp UL/94V-2 Fire Rated. Maximum bundle diameter: 1.7 cm, Product colour: Black, Material: Nylon. Width: 41 mm, Depth: 16 mm, Height: 25 mm. Package width: 300 mm, Package depth: 190 mm, Package height: 70 mm. Quantity per pack: 100 pc(s). Master (outer) case width: 446 mm, Master (outer) case length: 371 mm, Master (outer) case height: 433 mm



Features		Packaging data	
Product colour	Black	Package width	300 mm
Material	Nylon	Package depth	190 mm
Maximum bundle diameter *	1.7 cm	Package height	70 mm
Type	Cable clip	Package weight	497 g
Technical details		Packaging content	
Compliance certificates	RoHS	Quantity per pack	100 pc(s)
Weight & dimensions		Logistics data	
Width	41 mm	Master (outer) case width	446 mm
Depth	16 mm	Master (outer) case length	371 mm
Height	25 mm	Master (outer) case height	433 mm
Weight	4.8 g	Products per master (outer) case	30 pc(s)



0065030890397



065030890397

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.