



Everyday™ Black Toner by Xerox compatible with Brother TN-3280, High capacity

Brand : Xerox

Product family: Everyday

Product code: 006R03724

Product name : Everyday™
Black Toner by Xerox compatible
with Brother TN-3280, High
capacity

Everyday™ Black Toner by Xerox compatible with Brother TN-3280, High capacity

Everyday™ Black Toner by Xerox compatible with Brother TN-3280, High capacity:

Being environmentally responsible is simply the best way to do business, because it positively impacts the health of our planet, your company and your people. Everyday Remanufactured Toner by Xerox has the lowest carbon footprint than any single-use toner cartridge. Because you shouldn't have to choose between doing your part to reduce your eco-impact and your toner costs. And compatibility with the most popular printer brands means you can enjoy benchmark Xerox quality and stewardship no matter what kind of printer you have.

Everyday™ Black Toner by compatible with Brother TN-3280, High capacity. Black toner page yield: 8000 pages, Printing colours: Black, Quantity per pack: 1 pc(s)



Cut Toner Costs, Not Quality

Save big with 40-60% savings on major printer brands.

Features		Features	
Compatibility *	DCP-8060/DCP-8065DN	OEM code	TN-3280
	DCP-8070D/8080DN/8085DN	Product colour	Black
	HL-5240	Country of origin	China, Netherlands
	HL-5250DN/HL-5270DN/HL-5280DW	Weight & dimensions	
	HL-5340D/HL-5350DN	Height	185 mm
	HL-5370DW/HL-5380DN	Packaging data	
	MFC-8370DN/8880DN/8890DW	Package dimensions (W x D x H)	100.1 x 320 x 184.9 mm (3.94 x 12.6 x 7.28")
	MFC-8460N	Package weight (imperial)	1.06 kg (2.34 lbs)
	MFC-8480DN/MFC-8680DN	Package width	185 mm
	MFC-8690DW	Package depth	320 mm
Quantity per pack *	1 pc(s)	Package height	105 mm
Black toner cartridges quantity	1	Package weight	960 g
Black toner page yield *	8000 pages	Package type	Box
Type *	Compatible		
Printing colours *	Black		
Brand compatibility *	Brother		
Supply type *	Single pack		
Cartridge capacity	High (XL) Yield		



0095205895131



095205895131

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date