



Lenovo 4XF1K03170 monitor mount / stand 68.6 cm (27") Desk Black

Brand : Lenovo

Product code: 4XF1K03170

Product name : 4XF1K03170

- Rich monitor support scope
 - VESA bracket
 - Tilt & lift
 - One-step install TINY
 - Phone docking bar
- ThinkCentre TIO Flex

Lenovo 4XF1K03170 monitor mount / stand 68.6 cm (27") Desk Black:

The flexible compatibility of the new ThinkCentre TIO Flex makes it the perfect solution for your existing infrastructure while supporting future upgrades and expansions. TIO Flex integrates most Tiny PCs with 22" to 27" various monitors sizes, simplifying connections, minimising cables and enabling full access to Tiny's front ports.

Lenovo 4XF1K03170. Mounting: Screws, Maximum weight capacity: 5.5 kg, Minimum screen size: 55.9 cm (22"), Maximum screen size: 68.6 cm (27"), Maximum VESA mount: 100 x 100 mm. Tilt angle range: -5 - 22°. Product colour: Black



Mounting		Design	
Maximum weight capacity *	5.5 kg	Product colour *	Black
Minimum screen size *	55.9 cm (22")	Weight & dimensions	
Number of displays supported *	1	Width	250 mm
Maximum screen size *	68.6 cm (27")	Depth	480 mm
Mounting	Screws	Height	285 mm
Mounting type *	Desk	Weight	4 kg
Maximum VESA mount *	100 x 100 mm	Packaging data	
Ergonomics		Package width	480 mm
Height adjustment range	80 - 125 mm	Package depth	250 mm
Tilt adjustment	✓	Package height	285 mm
Tilt angle range	-5 - 22°	Package weight	4.25 kg
Cable management	✓	Operational conditions	
		Operating relative humidity (H-H)	5 - 95%



0195892064398



195892064398

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.