



## BenQ InstaShow WDC10C wireless presentation system USB Type-C

**Brand :** BenQ

**Product code:** 9H.JLD78.N3E

**Product name :** InstaShow WDC10C

IEEE 802.11ac 5GHz, AES 128 bit, 1080p, HDMI 1.4 (HDCP), USB Type-C

BenQ InstaShow WDC10C. Product colour: Black. Supported graphics resolutions: 800 x 600 (SVGA), 1024 x 768 (XGA), 1280 x 1024 (SXGA), 1280 x 720 (HD 720), 1280 x 768, 1280 x..., Supported video modes: 720p, 1080p, Maximum frame rate: 60 fps. Antenna type: Internal & external. Wi-Fi standards: Wi-Fi 5 (802.11ac), Wi-Fi data rate (max): 867 Mbit/s, Top Wi-Fi standard: Wi-Fi 5 (802.11ac). Interface: USB Type-C



| Design                         |                                                                                                                          | Power                               |             |
|--------------------------------|--------------------------------------------------------------------------------------------------------------------------|-------------------------------------|-------------|
| Product colour                 | Black                                                                                                                    | Power source type *                 | DC, USB     |
| LED indicators                 | ✓                                                                                                                        | Input voltage                       | 5 V         |
| Features                       |                                                                                                                          | System requirements                 |             |
| Supported graphics resolutions | 800 x 600 (SVGA), 1024 x 768 (XGA), 1280 x 1024 (SXGA), 1280 x 720 (HD 720), 1280 x 768, 1280 x                          | Windows operating systems supported | ✓           |
|                                | 800, 1280 x 960, 1360 x 768 (WXGA), 1400 x 1050 (SXGA+), 1440 x 900 (WXGA+), 1680 x 1050 (WSXGA+), 1920 x 1080 (HD 1080) | Mac compatibility                   | ✓           |
| Supported video modes          | 720p, 1080p                                                                                                              | Mac operating systems supported     | ✓           |
| Maximum frame rate             | 60 fps                                                                                                                   | Operational conditions              |             |
| Concurrent users               | 16 user(s)                                                                                                               | Operating temperature (T-T)         | 0 - 40 °C   |
| Security updates end date      | 31/12/2024                                                                                                               | Operating relative humidity (H-H)   | 10 - 80%    |
|                                |                                                                                                                          | Storage temperature (T-T)           | -10 - 60 °C |
|                                |                                                                                                                          | Storage relative humidity (H-H)     | 5 - 90%     |
| Management features            |                                                                                                                          | Weight & dimensions                 |             |
| Reset button                   | ✓                                                                                                                        | Weight                              | 1.27 kg     |
| Antenna                        |                                                                                                                          | Package width                       | 390 mm      |
| Antenna type                   | Internal & external                                                                                                      | Package depth                       | 485 mm      |
| Network                        |                                                                                                                          | Package height                      | 205 mm      |
| Wi-Fi standards                | Wi-Fi 5 (802.11ac)                                                                                                       | Package weight                      | 7.6 kg      |
| Wi-Fi data rate (max)          | 867 Mbit/s                                                                                                               | Packaging content                   |             |
| Top Wi-Fi standard             | Wi-Fi 5 (802.11ac)                                                                                                       | Cables included                     | HDMI, USB   |
| Frequency band                 | 5 GHz                                                                                                                    | Quick start guide                   | ✓           |
| Ethernet LAN                   | ✓                                                                                                                        | Logistics data                      |             |
| Ethernet LAN data rates        | 10,100 Mbit/s                                                                                                            | Country of origin                   | Taiwan      |
| Security algorithms            | 128-bit AES, WPA2, WPA2-Enterprise, WPA2-PSK                                                                             | Products per pallet                 | 144 pc(s)   |
| Maximum operating distance     | 8 m                                                                                                                      | Harmonized System (HS) code         | 8517620000  |

Ports & interfaces

|                            |            |
|----------------------------|------------|
| Interface *                | USB Type-C |
| Number of HDMI outputs     | 1          |
| HDMI version               | 1.4        |
| Ethernet LAN (RJ-45) ports | 1          |
| DC-in jack                 | ✓          |



4718755078804



0840046041380



840046041380

### Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.