



Lenovo 4X81L12874 stylus pen 3.8 g Black

Brand : Lenovo

Product code: 4X81L12874

Product name : 4X81L12874



- Diameter: 5.3 mm
 - Wacom AES 1.0
 - Up to 4096 levels of pressure sensitivity
 - Rapid charge 15s for more than 36 min operating time
 - More than 42 minutes active use for one single full charge in 5 minutes
 - Integrated storage and charging in notebook
- Integrated Pen for L13 Yoga Gen 3

Lenovo 4X81L12874 stylus pen 3.8 g Black:

Lenovo Integrated Pen for L13 Yoga Gen 3 with up to 4096 levels of pressure sensitivity, provides a natural pencil-like and paper experience when you sketch and jot down notes. Users will also enjoy easy access to short-cut functions through two built-in customisable buttons on the base of the pen. This pen can also be conveniently stored and charged in the notebook’s pen slot.

Lenovo 4X81L12874. Device compatibility: Laptop, Brand compatibility: Lenovo, Product colour: Black. Weight: 3.8 g, Width: 119.8 mm. Package type: Box, Package width: 219 mm, Package depth: 73 mm



Features		Weight & dimensions	
Device compatibility *	Laptop	Weight	3.8 g
Brand compatibility *	Lenovo	Width	119.8 mm
Compatibility	L13 Yoga Gen 3	Packaging data	
Product colour *	Black	Package type	Box
Tip colour	Black	Package width	219 mm
Pressure levels	4096	Package depth	73 mm
Battery type	Built-in	Package height	43 mm
Battery life	0.7 h	Package weight	60 g
Buttons quantity	2	Operational conditions	
Supported protocols	Wacom AES 1.0	Operating temperature (T-T)	5 - 40 °C
Certification	EU RoHS Ukraine RoHS USA:FCC Canada:ICES-003 EU:CE UK:UKCA EAC, SABS, VCCI, RCM CB, NOM-019	Operating relative humidity (H-H)	30 - 80%



0195892082293



195892082293

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.