

Philips S Line 242S9JML/00 computer monitor 61 cm (24") 1920 x 1080 pixels Full HD LCD Black

Brand : Philips

Product family: S Line

Product code: 242S9JML/00

Product name : 242S9JML/00

Business Monitor 242S9JML LCD monitor

Philips S Line 242S9JML/00 computer monitor 61 cm (24") 1920 x 1080 pixels Full HD LCD Black:

Our S Line monitor delivers business efficiency. Features like Flicker-free and LowBlue mode make work easy on the eyes and increase your productivity.

Philips S Line 242S9JML/00. Display diagonal: 61 cm (24"), Display resolution: 1920 x 1080 pixels, HD type: Full HD, Display technology: LCD, Response time: 4 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in speaker(s). Built-in USB hub, USB hub version: 3.2 Gen 1 (3.1 Gen 1). VESA mounting, Height adjustment. Product colour: Black



Display		Ergonomics	
Display diagonal *	61 cm (24")	Panel mounting interface	100 x 100 mm
Display resolution *	1920 x 1080 pixels	Cable lock slot *	✓
HD type *	Full HD	Cable lock slot type	Kensington
Native aspect ratio *	16:9	Height adjustment *	✓
Display technology *	LCD	Adjustable height (max)	13 cm
Panel type *	VA	Pivot	✓
Backlight type	W-LED	Pivot angle	-90 - 90°
Touchscreen *	✗	Swivelling	✓
Display brightness (typical)	300 cd/m²	Swivel angle range	-180 - 180°
Response time *	4 ms	Tilt adjustment	✓
Anti-glare screen	✓	Tilt angle range	-5 - 25°
Screen shape *	Flat	On Screen Display (OSD) languages	Simplified Chinese, Traditional Chinese, Czech, German, Dutch, English, Spanish, Finnish, French, Greek, Hungarian, Italian, Japanese, Korean, Polish, Portuguese, Russian, Swedish, Turkish, Ukrainian
Contrast ratio (typical) *	3000:1		
Contrast ratio (dynamic)	50000000:1		
Dynamic contrast ratio marketing name	SmartContrast		
Maximum refresh rate *	75 Hz	Plug and Play	✓
Viewing angle, horizontal	178°	LED indicators	Operation, Stand-by
Viewing angle, vertical	178°	Power	
Display number of colours *	16.7 million colours	Energy efficiency class (SDR) *	E
Pixel pitch	0.2745 x 0.2745 mm	Energy consumption (SDR) per 1000 hours *	21 kWh
Pixel density	93 ppi	Power consumption (typical) *	15 W
Viewable size, horizontal	52.7 cm	Power consumption (standby) *	0.4 W
Viewable size, vertical	29.6 cm	Power consumption (off)	0.3 W
Digital horizontal frequency	30 - 85 kHz	Power consumption (PowerSave)	12 W
Digital vertical frequency	48 - 75 Hz	AC input voltage	100 - 240 V
Display diagonal (metric)	60.5 cm	AC input frequency	50 - 60 Hz
DDC/CI	✓		
Haze rate	25%		

Display		Power	
Surface hardness	3H	Power supply type	Internal
Colour depth	8 bit	Operational conditions	
Colour gamut standard	sRGB	Operating temperature (T-T)	0 - 40 °C
sRGB coverage (typical)	99%	Storage temperature (T-T)	-20 - 60 °C
NTSC coverage (typical)	80%	Operating relative humidity (H-H)	20 - 80%
Display sRGB	✓	Operating altitude	0 - 3658 m
Performance		Non-operating altitude	3658 - 12192 m
VESA Adaptive Sync support	✓	Weight & dimensions	
Component video sync	Separate Sync, Sync-on-green (SOG)	Width (with stand)	539 mm
Flicker-free technology	✓	Depth (with stand)	205 mm
Low Blue Light technology	✓	Height (with stand)	484 mm
Multimedia		Weight (with stand)	4.85 kg
Number of speakers	2	Width (without stand)	539 mm
RMS rated power	2 W	Depth (without stand)	55 mm
Built-in speaker(s) *	✓	Height (without stand)	324 mm
Built-in camera *	✗	Weight (without stand)	3.09 kg
Design		Packaging data	
Market positioning *	Business	Package width	730 mm
Product colour *	Black	Package depth	139 mm
Front bezel colour	Black	Package height	420 mm
Feet colour	Black	Package weight	7.15 kg
Ports & interfaces		Packaging content	
Built-in USB hub *	✓	Stand included	✓
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Cables included	HDMI, DisplayPort, AC
USB upstream port type	USB Type-B	Manual	✓
Number of upstream ports	1	Bundled software	SmartControl
Number of USB Type-B upstream ports quantity	1	Sustainability	
USB Type-A downstream ports quantity	4	Sustainability compliance	✓
USB Power Delivery (USB PD)	✓	Sustainability certificates	ENERGY STAR, TCO
VGA (D-Sub) ports quantity	1	Doesn't contain	Mercury, PVC/BFR
DVI port	✓	Other features	
DVI-D ports quantity	1	Compatible operating systems	Windows 11 / 10 / 8.1 / 8 / 7 Mac OS X
HDMI *	✓	Exterior finish type	Textured
HDMI ports quantity	1	Picture enhancement	SmartImage
HDMI version	1.4	Regulatory Approvals	CB; CE Mark; CU-EAC; EAEU RoHS; FCC Class B; ICES-003; SEMKO; TUV Ergo; TUV/GS
DisplayPorts quantity	1	Heavy metals free	Hg (mercury)
DisplayPort version	1.2	EasyRead mode	✓
Audio output	✓	LowBlue mode	✓
PC Audio in	✓	Compliance certificates	RoHS
HDCP	✓	Mean time between failures (MTBF)	70000 h
HDCP version	1.4	Recycling data	
Ergonomics		Recyclable packaging material	100%
VESA mounting *	✓	Post-consumer recycled plastic	85%



8712581796464

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.