

## Viewsonic PJ-WMK-304 project mount Wall White

**Brand :** Viewsonic

**Product code:** PJ-WMK-304

**Product name :** PJ-WMK-304

25kg, 366-635mm, White

[Viewsonic PJ-WMK-304 project mount Wall White:](#)

With the ViewSonic® PJ-WMK-304 Universal Wall Mount Kit, you can easily install select ViewSonic® ultra-short-throw projectors just inches away from a wall. This simple and flexible set up will not only help to produce a large image from a short distance but also keeps the projector up and out of the way for a more subtle presence. Compatible with: LS810, LS820, LS830, PX800HD, PS700X, and PS700W. Viewsonic PJ-WMK-304. Mounting type: Wall, Maximum weight capacity: 25 kg, Product colour: White. Weight: 4.3 kg, Package width: 495 mm, Package depth: 207 mm. Products per master (outer) case: 1 pc(s)



### Performance

|                            |                                              |
|----------------------------|----------------------------------------------|
| Mounting type *            | Wall                                         |
| Maximum weight capacity *  | 25 kg                                        |
| Product colour *           | White                                        |
| Telescopic                 | ✓                                            |
| Adjustable arm             | ✓                                            |
| Distance to the wall (min) | 36.6 cm                                      |
| Distance to the wall (max) | 63.5 cm                                      |
| Compatible products        | LS810, LS820, LS830, PX800HD, PS700X, PS700W |

### Weight & dimensions

|                |        |
|----------------|--------|
| Weight         | 4.3 kg |
| Package width  | 495 mm |
| Package depth  | 207 mm |
| Package height | 203 mm |
| Package weight | 5 kg   |

### Logistics data

|                                  |            |
|----------------------------------|------------|
| Products per master (outer) case | 1 pc(s)    |
| Harmonized System (HS) code      | 8302500000 |



0766907978711



766907978711

### Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.