



Everyday™ Magenta Toner by Xerox compatible with HP 971XL (CN627AE, CN627A, CN627AM), High capacity

Brand : Xerox

Product family: Everyday

Product code: 006R04597

Product name : Everyday™
Magenta Toner by Xerox
compatible with HP 971XL
(CN627AE, CN627A, CN627AM),
High capacity

Everyday™ Magenta Toner by Xerox compatible with HP 971XL (CN627AE, CN627A, CN627AM), High capacity

Everyday™ Magenta Toner by Xerox compatible with HP 971XL (CN627AE, CN627A, CN627AM), High capacity:

Being environmentally responsible is simply the best way to do business, because it positively impacts the health of our planet, your company and your people. Everyday Remanufactured Toner by Xerox has the lowest carbon footprint than any single-use toner cartridge. Because you shouldn't have to choose between doing your part to reduce your eco-impact and your toner costs. And compatibility with the most popular printer brands means you can enjoy benchmark Xerox quality and stewardship no matter what kind of printer you have.

Everyday™ Magenta Toner by compatible with HP 971XL (CN627AE, CN627A, CN627AM), High capacity. Black toner page yield: 6600 pages, Colour toner page yield: 6600 pages, Printing colours: Magenta, Quantity per pack: 1 pc(s)



Cut Toner Costs, Not Quality

Save big with 40-60% savings on major printer brands.

Features		Features	
Compatibility *	Laser MFP X451 Laser MFP X476 Laser MFP X551 Laser MFP X576	OEM code	CN627AE, CN627A, CN627AM
Quantity per pack *	1 pc(s)	Country of origin	China
Colour toner cartridges quantity	1	Weight & dimensions	
Black toner page yield *	6600 pages	Weight	223 g
Colour toner page yield *	6600 pages	Packaging data	
Type *	Compatible	Package width	50 mm
Printing colours *	Magenta	Package depth	225 mm
Brand compatibility *	HP	Package height	35 mm
Supply type *	Single pack	Package weight	210 g
Cartridge capacity	High (XL) Yield	Logistics data	
Replacement for	HP 971XL	Export Control Classification Number (ECCN)	EAR99
		Harmonized System (HS) code	84439990



0095205037562



095205037562

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date