

ASUS MB16AH computer monitor 39.6 cm (15.6") 1920 x 1080 pixels Full HD Black, Grey

Brand : ASUS

Product code: 90LM04T0-B02170

Product name : MB16AH

- USB-C and micro-HDMI ports provide versatile connectivity with laptops, game consoles, and cameras
 - Can automatically sense its orientation and switch the monitor between landscape and portrait modes
 - 15.6-inch Full HD portable anti-glare IPS display with an ultra-slim design helps you get things done more efficiently when you're on the go
 - Foldable sleeve case can be turned into a stand to prop the monitor up in either portrait or landscape mode
 - ASUS Eye Care monitors feature TÜV Rheinland-certified Flicker-free and Low Blue Light technologies to ensure a comfortable viewing experience
- 15.6", 1920 x 1080, IPS, 220 cd/m², Full HD, 5ms, 16:9
ASUS MB16AH. Display diagonal: 39.6 cm (15.6"), Display resolution: 1920 x 1080 pixels, HD type: Full HD, Display surface: Matt, Response time: 5 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in speaker(s). Product colour: Black, Grey



Display		Ports & interfaces	
Display diagonal *	39.6 cm (15.6")	Built-in USB hub *	✗
Display resolution *	1920 x 1080 pixels	HDMI *	✓
HD type *	Full HD	HDMI ports quantity	1
Native aspect ratio *	16:9	Micro HDMI ports quantity	1
Panel type *	IPS	Headphone out *	✓
Backlight type	LED	Headphone outputs	1
Touchscreen *	✗	HDCP	✓
Display brightness (typical)	220 cd/m²	Ergonomics	
Response time *	5 ms	VESA mounting *	✗
Display surface	Matt	Height adjustment *	✗
Anti-glare screen	✓	Power	
Screen shape *	Flat	Energy efficiency class (SDR) *	E
Aspect ratio	16:9	Energy consumption (SDR) per 1000 hours *	10 kWh
Contrast ratio (typical) *	700:1	Power consumption (typical) *	10 W
Maximum refresh rate *	60 Hz	Power consumption (standby) *	0.3 W
Viewing angle, horizontal	178°	Power consumption (off)	0.2 W
Viewing angle, vertical	178°	AC input voltage	100 - 240 V
Display number of colours *	262000 colours	AC input frequency	50 - 60 Hz
Performance		Energy efficiency scale	A to G
NVIDIA G-SYNC *	✗	Weight & dimensions	
AMD FreeSync *	✗	Width (with stand)	359.8 mm
Flicker-free technology	✓	Depth (with stand)	9 mm
Multimedia		Height (with stand)	227.6 mm
Number of speakers	2	Weight (with stand)	730 g
RMS rated power	1 W	Packaging content	
Built-in speaker(s) *	✓	Stand included	✓
Built-in camera *	✗	Cables included	AC, HDMI, Micro-HDMI, USB Type-C, USB Type-C to USB Type-A
Design			
Market positioning *	Business		

Design		Logistics data	
Product colour *	Black, Grey	Harmonized System (HS) code	85285210



4718017705301



0192876705308



192876705308



0195553404433



195553404433

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.