



Lenovo 4X20S56705 power adapter/inverter Indoor 170 W Black

Brand : Lenovo

Product code: 4X20S56705

Product name : 4X20S56705



- 170W wattage
 - 30% size reduction compared to ThinkPad Standard 170W AC adapter
 - Compatible with ThinkPad Mobile Workstation Machines with a rectangular "Slim Tip" power plug
- ThinkPad Mobile Workstation Slim 170W AC Adapter (Slim-tip) - UK/HK/SGP/SRI

Lenovo 4X20S56705 power adapter/inverter Indoor 170 W Black:

The ThinkPad 170W Slim AC adapter is the new adapter with a slim and small design. It is the perfect replacement or spare power adapter for your ThinkPad Mobile Workstation machines.

Lenovo 4X20S56705. Purpose: Laptop, Power supply type: Indoor, Input voltage: 100 - 240 V. Product colour: Black. Certification: C/UL CB/CE/PSE/IRAM NOM/NRCan FCC & ICES Mexico Energy Consumption PSB/CCC/CECP KC/KCC South Korea.... Cable length: 1.5 m, Width: 150 mm, Depth: 77 mm. Package width: 264 mm, Package depth: 110 mm, Package height: 53 mm

Features		Certificates	
Purpose *	Laptop	Certification	C/UL CB/CE/PSE/IRAM NOM/NRCan
Power supply type *	Indoor		FCC & ICES Mexico Energy
Input voltage *	100 - 240 V		Consumption PSB/CCC/CECP KC/KCC
Input frequency *	50 - 60 Hz		South Korea MEPS RCM Australia
Output power *	170 W		GEMS BSMI/EAC/GS/Serbia
Output current	2.5 A		Ukraine/SII/NRCS SIRIM/ST
Brand compatibility	Lenovo		ISC/SONCAP UZBEK/INSM/KUCAS
Compatibility	ThinkPad		BIS/Morocco
Design		Weight & dimensions	
Product colour *	Black	Cable length	1.5 m
		Width	150 mm
		Depth	77 mm
		Height	22 mm
		Weight	440 g
Operational conditions		Packaging data	
Operating temperature (T-T)	0 - 40 °C	Package width	264 mm
Operating relative humidity (H-H)	8 - 80%	Package depth	110 mm
		Package height	53 mm
		Package weight	750 g
		Package type	Box
		Packaging content	
		Quantity per pack *	1 pc(s)



0194552765316



194552765316

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.