

Brother LC1100BKBP2 ink cartridge 2 pc(s) Original Black

Brand : Brother

Product code: LC1100BKBP2

Product name : LC1100BKBP2

- Black cartridge prints 450 pages in accordance with ISO/IEC 24711
 - High quality genuine Brother cartridge
 - Prevents waste to save you paper, time and money
 - Genuine Brother ink cartridges are rigorously tested to print perfectly every time saving you time and money
 - Using Brother LC1100 original ink cartridges protects your printer warranty
- The Brother LC1100BKBP2 Black Ink Cartridge Twin Pack. Each black cartridge prints 450 pages.

Brother LC1100BKBP2 ink cartridge 2 pc(s) Original Black:

Purchase the LC1100BKBP2 Black Ink Cartridge Twin Pack to save money on your genuine Brother cartridges. Developed to ensure you always get quality documents, you'll be protecting your printer from potential long-term damage caused by using non-genuine products.
Brother LC1100BKBP2. Black ink type: Pigment-based ink, Supply type: Twin pack, Printing colours: Black, Quantity per pack: 2 pc(s), Black ink page yield: 450 pages



Features		Weight & dimensions	
Black ink type	Pigment-based ink	Width	165 mm
Print technology	Inkjet printing	Depth	50 mm
Compatibility *	DCP-185C DCP-385C DCP-395CN	Height	125 mm
	DCP-585CW DCP-6690CW DCP-7715W MFC-490CW MFC-5490CN	Weight	109 g
	MFC-5890CN MFC-6490CW	Packaging data	
	MFC-6890CDW MFC-790CW MFC-795CW MFC-990CW	Package dimensions (WxDxH)	57 x 122 x 178 mm
Quantity per pack *	2 pc(s)	Package weight	137 g
Black ink cartridges quantity	2	Logistics data	
Black ink page yield *	450 pages	Pallet gross height	16.5 cm
Approximate page yield (A4, black & white, ISO/IEC 19752)	450 pages	Products per pallet	960 pc(s)
Type *	Original	Master (outer) cases per pallet	240 pc(s)
Ink type	Pigment-based ink	Layers per pallet	8 pc(s)
Printing colours *	Black	Master (outer) cases per pallet layer	30 pc(s)
Brand compatibility *	Brother	Pallet gross weight	159.6 kg
Supply type *	Twin pack	Harmonized System (HS) code	84439990
Country of origin	Malaysia	Pallet type	1200 x 1000 mm
Colour	✗		



5014047561238

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.