

Epson Screen (50" Desktop type) - ELPSC32

Brand : Epson

Product code: V12H002S32

Product name : Screen (50" Desktop type) - ELPSC32



Screen (50" Desktop type) - ELPSC32

Epson Screen (50" Desktop type) - ELPSC32:

No more big black boxes
There's no need to let a big, black TV screen permanently dominate your space. By using a non-fixed screen and projector, you'll have the flexibility to view content on a big screen when you need it and hide it away when it's not in use.

Make the most of your projector
Don't settle for projecting on to a bare wall – with our screens you can enjoy the exceptional detail, vibrant colours, defined shadows and deep blacks that your projector provides.

Fuss-free assembly
Forget complicated instructions and lengthy installations, our screens are quick and easy to assemble. Just like our projectors, Epson screens are designed to get you up and running with minimal fuss. What's more, they're also easy to stow away.

Flexible positioning
Our versatile screens can be used in almost any room and can be easily adjusted so that you can get the best out of your projector.

Performance		Logistics data	
Format	Wide	Products per pallet	64 pc(s)
Diagonal *	127 cm (50")	Pallet gross length	120 cm
Country of origin	China	Pallet gross width	80 cm
Design		Pallet gross height	2.15 m
Mounting type *	Wall	Products per pallet layer	4 pc(s)
Product colour	Black, White	Products per pallet layer (UK)	6 pc(s)
Packaging data		Products per pallet (UK)	96 pc(s)
Quantity per pack	1 pc(s)	Pallet length (UK)	120 cm
Package width	120 mm	Pallet width (UK)	100 cm
Package depth	925 mm	Pallet height (UK)	2.15 m
Package height	185 mm	Harmonized System (HS) code	90106000
Package weight	3.84 g		

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date