



Canon BCI-3eM ink cartridge 1 pc(s) Original Magenta

Brand : Canon
Product code: 4481A002
Product name : BCI-3eM

Inktcartridge BCI-3EM refill

Canon BCI-3eM ink cartridge 1 pc(s) Original Magenta:

Canon has poured all the Know How of its extraordinary history of developing innovative office machines into each of its copiers, printers, and networked office systems. The same superiority of design and manufacture goes into all of the Canon-branded consumable imaging supplies and parts for this equipment. Naturally, no one makes better parts and supplies for Canon products than Canon. Using genuine Canon parts and supplies is your best insurance against equipment damage, and possibly voiding your equipment warranty.
For BJC 3000/BJC 3010/BJC 6000, i550/i560/i850/i860, MultiPASS C755/F30/F50/F60/F80/MP700, S400/S450/S500/S520/S530D/S600/S630/S630 Network/ S750
Canon BCI-3eM. Colour ink type: Pigment-based ink, Printing colours: Magenta, Quantity per pack: 1 pc(s)



Features		Features	
Colour ink type	Pigment-based ink	Brand compatibility *	Canon
Print technology	Inkjet printing	Colour	✓
Compatibility *	i550, i850, MultiPASS C755, MultiPASS F30, MultiPASS F50, MultiPASS F60, MultiPASS F80, MultiPASS MP700, MultiPASS MP730, S400, S450, S500, S520, S530D, S600, S630, S630 Network, S750	Operational conditions	
		Operating relative humidity (H-H)	10 - 80%
Quantity per pack *	1 pc(s)	Operating temperature (T-T)	5 - 35 °C
Type *	Original	Other features	
Ink type	Pigment-based ink	Page yield footnote	310
Printing colours *	Magenta	Maximum duty cycle	3560 pages per month
		Logistics data	
		Harmonized System (HS) code	84439990



7508457257976



2001133195005



4960999866611



4960999865287



5704327122692



4960999866673



4960999171661

Catalog Object Cloud



Disclaimer: The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.