

Lenovo Nvidia T1000 8 GB GDDR6

Brand : Lenovo

Product code: 4X61J52233

Product name : Nvidia T1000



- 8GB of GDDR6 memory
 - Peak memory bandwidth up to 160GB/s
 - Support 4 simultaneous display and up to 5K resolution with VESA® DisplayPort® connectors
 - DisplayPort with audio
 - PCI Express Interface: PCIe 3.0 x 16
- Nvidia T1000 8GB 4xMDP

Lenovo Nvidia T1000 8 GB GDDR6:

Nvidia T1000 8GB 4xMDP Graphics Card is powered by NVIDIA Turing graphics processing unit (GPU) technology and 8GB of GGDR6 memory. The NVIDIA T1000 graphics board is targeted for professional CAD, DCC and visualization designers, engineers, and users. Get the budget friendly high performing graphics board to drive today's demanding professional workflows in a compact footprint. Lenovo Nvidia T1000. Graphics processor family: NVIDIA, Graphics processor: T1000. Discrete graphics card memory: 8 GB, Graphics card memory type: GDDR6. Maximum resolution: 7680 x 4320 pixels. Interface type: PCI Express x16 3.0. Cooling type: Active, Number of fans: 1 fan(s)

Processor		Design	
Graphics processor family *	NVIDIA	Number of slots	1
Graphics processor *	T1000	Certification	BSMI, FCC, ICES, CE, VCCI, KCC, RCM, CB, Morocco
Maximum resolution *	7680 x 4320 pixels		
Memory		Power	
Discrete graphics card memory *	8 GB	Power consumption (max)	50 W
Graphics card memory type *	GDDR6		
Memory bandwidth (max)	160 GB/s		
Ports & interfaces		System requirements	
Interface type *	PCI Express x16 3.0	Windows operating systems supported	✓
Mini DisplayPorts quantity	4		
DisplayPort version	1.4a		
Design		Weight & dimensions	
Cooling type *	Active	Weight	136 g
Number of fans	1 fan(s)	Length	155.9 mm
		Height	68.9 mm
		Packaging data	
		Package width	325 mm
		Package depth	195 mm
		Package height	85 mm



0195892052913



195892052913

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.