

Epson EH-TW7100 Standard throw projector 3000 ANSI lumens 3LCD 3D White



Brand : Epson

Product code: V11H959041

Product name : EH-TW7100

- 4K PRO-UHD for crisp, clear images: Watch native 4K and upscale non-4K content
 - Easy to set up and access content: Stream content by plugging devices into either of the two HDMI ports
 - High-quality and affordable: Flexible features that deliver a 4K experience at an affordable price
 - Engaging big screen experience: Get the best out of movies, sports and gaming
 - Watch a movie a day for seven years: 5,000 hours lamp life in Eco mode
- EH-TW7100, 3LCD, 3000 lum, 4K PRO-UHD, 16:9, 100000:1, USB 2.0, HDMI, Bluetooth, 410x310x157 mm

Projector		Storage	
Screen size compatibility *	1016 - 12700 mm (40 - 500")	Card reader integrated *	✗
Projection distance	2.95 - 4.77 m	Features	
Projector brightness *	3000 ANSI lumens	Noise level (economic mode)	24 dB
Projection technology *	3LCD	Noise level *	32 dB
Contrast ratio (typical) *	100000:1	Country of origin	Philippines
Native aspect ratio *	16:9	Multimedia	
Number of colours	1.073 billion colours	Built-in speaker(s) *	✓
Keystone correction, horizontal	-30 - 30°	RMS rated power	10 W
Keystone correction, vertical	-30 - 30°	Design	
Matrix size	1.55 cm (0.61")	Market positioning *	Home cinema
Light source		Product type *	Standard throw projector
Light source type *	Lamp	Product colour *	White
Service life of light source *	3500 h	Placement	Desktop, Ceiling
Service life of light source (economic mode)	5000 h	Cable lock slot	✓
Lamp type	UHE	Cable lock slot type	Kensington
Lamp power	250 W	Display	
Lamps quantity	1 lamp(s)	Built-in display *	✗
Lens system		Power	
Focus *	Manual	Power source *	AC
Focal length range	18.2 - 29.2 mm	Power consumption (typical) *	387 W
Aperture range (F-F)	1.49 - 1.77	Power consumption (standby) *	0.5 W
Zoom capability	✓	Power consumption (economy mode)	297 W
Zoom type	Manual	AC input voltage	100 - 240 V
Zoom ratio	1:1.62	AC input frequency	50 - 60 Hz
Throw ratio	1.32 - 2.15:1	Operational conditions	
Horizontal lens shift range	-24 - 24%	Operating temperature (T-T)	5 - 30 °C
Vertical lens shift range	-60 - 60%	Storage temperature (T-T)	-10 - 60 °C
Video		Operating relative humidity (H-H)	20 - 80%
Full HD *	✓	Storage relative humidity (H-H)	10 - 90%
3D *	✓	Weight & dimensions	
Supported 3D formats	Side by side, Top and bottom	Width	410 mm
Video colour modes	Auto, Bright cinema, Cinema, Dynamic, Natural	Depth	310 mm
Ports & interfaces		Height	157 mm
HDMI connector type	Full-size	Weight *	6.9 kg
USB 2.0 ports quantity	2	Package width	495 mm
Mini-USB 2.0 ports quantity	1		

Ports & interfaces		Weight & dimensions	
Serial interface type *	RS-232C	Package depth	500 mm
PC Audio out	✓	Package height	235 mm
HDMI ports quantity *	2	Package weight	8.95 kg
DVI port *	✗	Packaging content	
AC (power) in	✓	Remote control included *	✓
Network		Cables included	AC
Smart TV *	✗	Manual	✓
Ethernet LAN *	✗	Logistics data	
Wi-Fi *	✗	Quantity per pack	1 pc(s)
Bluetooth	✓	Harmonized System (HS) code	85286200



8715946670850

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.