

Brother LC3233M ink cartridge 1 pc(s) Original Standard Yield Magenta

Brand : Brother

Product code: LC3233M

Product name : LC3233M

- Magenta
 - Prints 1500 pages in accordance with ISO/IEC24711
 - High quality, genuine Brother cartridge
 - Simple Cartridge' technology - transparent cartridge so you can gauge how much ink is inside
 - Prevents waste to save you paper, time and money
- Genuine Brother LC3233M high yield magenta ink cartridge - single pack. Prints up to 1500 pages.

Brother LC3233M ink cartridge 1 pc(s) Original Standard Yield Magenta:

The LC3233M is a high yield magenta ink cartridge that prints up to 1500 pages. As a genuine, expertly tested and designed Brother product, you can feel confident you're getting the best possible quality and value from your printouts.

Brother LC3233M. Colour ink type: Pigment-based ink, Cartridge capacity: Standard Yield, Supply type: Single pack, Colour ink page yield: 1500 pages, Printing colours: Magenta, Quantity per pack: 1 pc(s)



Features		Weight & dimensions	
Colour ink type	Pigment-based ink	Height	120 mm
Print technology	Inkjet printing	Weight	66 g
Compatibility *	MFC-J1300DW DCP-J1100DW	Packaging data	
Quantity per pack *	1 pc(s)	Package weight	87 g
Colour ink cartridges quantity	1	Other features	
Colour ink page yield *	1500 pages	Certification	ISO/IEC 24711
Type *	Original	Logistics data	
Cartridge capacity	Standard Yield	Pallet gross height	15.9 cm
Ink type	Pigment-based ink	Products per pallet	2800 pc(s)
Printing colours *	Magenta	Master (outer) cases per pallet	28 pc(s)
Brand compatibility *	Brother	Layers per pallet	4 pc(s)
Supply type *	Single pack	Master (outer) cases per pallet layer	7 pc(s)
Country of origin	Philippines	Pallet gross weight	246.5 kg
Weight & dimensions		Harmonized System (HS) code	84439990
Width	15 mm	Pallet type	800 x 1200 mm
Depth	85 mm		



4977766787260



5715328103382

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.