



HP Scanjet Pro 2600 f1 Flatbed & ADF scanner 600 x 600 DPI A4 White

Brand : HP

Product family: Scanjet

Product code: 20G05A#B19

Product name : Scanjet Pro 2600 f1



Enhance productivity with fast, two-sided scanning, a 60-page ADF, and one-button shortcuts.

HP Scanjet Pro 2600 f1 Flatbed & ADF scanner 600 x 600 DPI A4 White:

Boost productivity for professional scanning tasks with the compact, reliable HP ScanJet Pro, designed for scanning up to 1,500 pages daily. Automate workflows with one-click shortcuts and fast, two-sided scanning from the auto document feeder.

HP Scanjet Pro 2600 f1. Maximum scan size: 89 x 148 mm, Optical scanning resolution: 600 x 600 DPI, Enhanced scan resolution: 1200 x 1200 DPI. Scanner type: Flatbed & ADF scanner, Product colour: White. Sensor type: CIS, Daily duty cycle (max): 1500 pages, Maximum image resolution: 1200 x 1200 pixels. Auto document feeder (ADF) input capacity: 60 sheets. Maximum ISO A-series paper size: A4, ISO A-series sizes (A0...A9): A5, A6, ISO B-series sizes (B0...B9): B5

Scanning		Paper handling	
Maximum scan size *	89 x 148 mm	ISO B-series sizes (B0...B9)	B5
Optical scanning resolution *	600 x 600 DPI	Ports & interfaces	
Enhanced scan resolution	1200 x 1200 DPI	USB port *	✓
Colour scanning	✓	USB version	2.0
Duplex scanning *	✓	Power	
Input colour depth	48 bit	Power supply type *	AC
Output colour depth	24 bit	Power consumption (typical)	12.9 W
ADF scan speed (b/w, A4)	25 ppm	Power consumption (standby)	5 W
ADF scan speed (colour, A4)	50 ppm	Power consumption (off)	0.06 W
Design		Sleep mode	✓
Scanner type *	Flatbed & ADF scanner	Input voltage	100 - 240 V
Product colour *	White	Auto power off	✓
Built-in display *	✓	Weight & dimensions	
Performance		Width	491.5 mm
Sensor type *	CIS	Depth	325.4 mm
Maximum image resolution	1200 x 1200 pixels	Height	133.3 mm
Scan file formats	BMP, CSV, DOC, DOCX, JPEG, PDF, PNG, RTF, TIFF, XLS	Weight	5.4 kg
Daily duty cycle (max) *	1500 pages	Packaging data	
Built-in OCR	✓	Quantity per pack	1 pc(s)
Button functions	Cancel, Color scan, Off, On	Package width	600 mm
Scan drivers	TWAIN	Package depth	245 mm
Input capacity		Package height	499 mm
Auto document feeder (ADF) input capacity	60 sheets	Package weight	7.3 kg
Paper handling		Packaging content	
Maximum ISO A-series paper size *	A4	Cables included	AC, USB
ISO A-series sizes (A0...A9)	A5, A6	Logistics data	
		Country of origin	China, Taiwan
		Harmonized System (HS) code	84716070



0195697673863



195697673863

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.