



Lenovo 4XC7A79699 network card Internal Ethernet 10000 Mbit/s

Brand : Lenovo

Product code: 4XC7A79699

Product name : 4XC7A79699




ThinkSystem Intel X710-T4L 10GBase-T 4-Port PCIe Ethernet Adapter

Lenovo 4XC7A79699 network card Internal Ethernet 10000 Mbit/s:

The Intel X710 family of 10 Gigabit Ethernet (GbE) server network adapters addresses the demanding needs of the next-generation data center. By providing unmatched features for server and network virtualization, small packet performance, and low power; the data center network is flexible, scalable, and resilient.

Lenovo 4XC7A79699. Internal. Connectivity technology: Wired, Host interface: PCI Express, Interface: Ethernet. Maximum data transfer rate: 10000 Mbit/s. Product colour: Multicolour

Ports & interfaces		Design	
Connectivity technology *	Wired	Internal *	✓
Host interface *	PCI Express		
Interface *	Ethernet	Certification	IEC 68, FCC Part 68.302, NISTA, 1A EN55022 EN55024 EN 61000-3-2 EN 61000-3-3 ICES-003, Issue-004 FCC 47 CFR Part 15 Class A VCCI AS/NZS CISPR 22 / C-tick RRL for KC BSMI UL 94 V-1
Ethernet LAN (RJ-45) ports	4		
PCI version	3.0		
PCI Card form factor	Full-height		
Network		Operational conditions	
Maximum data transfer rate *	10000 Mbit/s	Operating temperature (T-T)	0 - 55 °C
Networking standards *	IEEE 802.1Q, IEEE 802.1p, IEEE 802.3x	Storage temperature (T-T)	-20 - 65 °C
Ethernet LAN	✓	Operating relative humidity (H-H)	5 - 80%
Ethernet interface type	10 Gigabit Ethernet	Storage relative humidity (H-H)	5 - 95%
Ethernet LAN data rates	10,100,1000,10000 Mbit/s	Weight & dimensions	
Cabling technology	10/100/1000BaseT(X)	Width	15 mm
Design		Depth	167 mm
Component for *	Server/workstation	Height	69 mm
Product colour	Multicolour		



0889488597796



889488597796

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.