



APC NetShelter SX, Server Rack Enclosure, 48U, White, 2258H x 750W x 1200D mm

Brand : APC

Product code: AR3357W

Product name : APC NetShelter SX, Server Rack Enclosure, 48U, White, 2258H x 750W x 1200D mm

APC NetShelter SX, Server Rack Enclosure, 48U, White, 2258H x 750W x 1200D mm

APC NetShelter SX, Server Rack Enclosure, 48U, White, 2258H x 750W x 1200D mm:

AR3357W Features


- NetShelter SX 48U 750mm Wide x 1200mm Deep Enclosure, SE White
 - Feature-rich custom-configured or pre-integrated cabinets tailored to your specific needs.
 - Includes: Baying hardware, Documentation CD, Key(s), Leveling feet, Mounting hardware, Pre-installed casters, Side panels, User Manual
- APC NetShelter SX, Server Rack Enclosure, 48U, White, 2258H x 750W x 1200D mm. Type: Freestanding rack, Rack capacity: 48U, Maximum weight capacity: 1704 kg, International Protection (IP) code: IP20. Weight: 185.4 kg



Features		Weight & dimensions	
Rack capacity *	48U	Height	2258 mm
Type *	Freestanding rack	Weight	185.4 kg
Maximum weight capacity *	1704 kg	Mounting depth (min)	26.2 cm
Maximum weight capacity (rolling)	1022 kg	Mounting depth (max)	104.8 cm
International Protection (IP) code	IP20	Packaging data	
Weight & dimensions		Package width	895 mm
Width	750 mm	Package depth	1334 mm
Depth	1200 mm	Package height	2400 mm
		Package weight	201.8 kg
		Logistics data	
		Harmonized System (HS) code	85381000



0731304324614



731304324614

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.