

ASUS ThunderboltEX 4 interface cards/adaptor Internal Mini DisplayPort, PCIe, Thunderbolt, USB 2.0, USB 3.2 Gen 2 (3.1 Gen 2)

Brand : ASUS

Product code: 90MC09P0-M0EAY0

Product name : ThunderboltEX 4

- Intel®-certified Thunderbolt™ 4 add-on card
 - 40 Gbps bi-directional bandwidth for superfast data transfers and video output
 - Dual Thunderbolt™ 4 ports (USB-C®), with support for up to five Thunderbolt devices in a daisy chain
 - DisplayPort™ 1.4 for 8K Ultra HD support
- Intel Thunderbolt 4 JHL8540, 2 x USB Type-C (Thunderbolt 4), 2 x mini DisplayPort, 1 x 6-pin PCIe, 1 x USB 2.0 header, 1 x Thunderbolt header, PCIe 3.0 x4


ASUS ThunderboltEX 4 interface cards/adaptor Internal Mini DisplayPort, PCIe, Thunderbolt, USB 2.0, USB 3.2 Gen 2 (3.1 Gen 2):

Enable blisteringly fast speeds and any-way-up connectivity

ASUS ThunderboltEX 4 is a Thunderbolt™ 4 add-on card that offers 40 Gbps bi-directional bandwidth, USB4™ device compatibility, and DisplayPort™ 1.4. It supports up to five Thunderbolt devices in a daisy chain and enables up to 100-watt USB-C® charging for laptops.



Ports & interfaces		System requirements	
Host interface *	PCIe	Windows operating systems supported	Windows 10 x64
Output interface *	Mini DisplayPort, PCIe, Thunderbolt, USB 2.0, USB 3.2 Gen 2 (3.1 Gen 2)	Weight & dimensions	
Expansion card standard	PCIe 3.0	Width	117.7 mm
USB 2.0 ports quantity	1	Depth	180.5 mm
USB 3.2 Gen 2 (3.1 Gen 2) Type-C ports quantity	2	Packaging data	
Design		Quantity	1
Internal *	✓	Cables included	Mini DisplayPort, Thunderbolt, USB
Product colour	Black	Drivers included	✓
Purpose	PC	Manual	✓
Features		Package type	Box
Chipset	Intel Thunderbolt 4 JHL8540	Logistics data	
Data transfer rate (max)	40 Gbit/s	Harmonized System (HS) code	84733020
Plug and Play	✓	Other features	
		Maximum resolution	7680 x 4320 pixels
		Compatibility	ASUS Intel 500



4711081115243



0195553115254



195553115254

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.