



Lenovo ThinkVision E20-30 49.5 cm (19.5") 1600 x 900 pixels HD+ LED



Brand : Lenovo

Product family: ThinkVision

Product code: 62F7KAT4UK

Product name : ThinkVision
E20-30 49.5 cm (19.5") 1600 x
900 pixels HD+ LED

- 49.5cm (19.5") HD+ 1600 x 900 W-LED TN
- 5ms, 16:9, 250cd/m², 1000:1
- VGA, HDMI

49.5cm (19.5") HD+ 1600 x 900 W-LED TN, 16:9, 250cd/m², 16.7M, 5ms, 170°/160°, 1000:1
Lenovo ThinkVision E20-30 49.5 cm (19.5") 1600 x 900 pixels HD+ LED. Display diagonal: 49.5 cm (19.5"), Display resolution: 1600 x 900 pixels, HD type: HD+, Display technology: LED, Response time: 5 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 170°, Viewing angle, vertical: 160°. VESA mounting. Product colour: Black

Display		Ergonomics	
Display diagonal *	49.5 cm (19.5")	Cable lock slot type	Kensington
Display resolution *	1600 x 900 pixels	Height adjustment *	✗
HD type *	HD+	Tilt adjustment	✓
Native aspect ratio *	16:9	Tilt angle range	-5 - 22°
Display technology *	LED	On Screen Display (OSD)	✓
Panel type *	TN	Power	
Backlight type	W-LED	Energy efficiency class (SDR) *	D
Touchscreen *	✗	Energy consumption (SDR) per 1000 hours *	11 kWh
Display brightness (typical)	250 cd/m ²	Power consumption (typical) *	12 W
Response time *	5 ms	Power consumption (standby) *	0.5 W
Anti-glare screen	✓	Power consumption (max)	15 W
Screen shape *	Flat	Power consumption (off)	0.3 W
Contrast ratio (typical) *	1000:1	AC input voltage	100 - 240 V
Contrast ratio (dynamic)	3000000:1	AC input frequency	50 - 60 Hz
Maximum refresh rate *	60 Hz	Energy efficiency scale	A to G
Viewing angle, horizontal	170°	Weight & dimensions	
Viewing angle, vertical	160°	Width (with stand)	464.8 mm
Display number of colours *	16.7 million colours	Depth (with stand)	180.4 mm
Response time (fast)	2 ms	Height (with stand)	352.6 mm
Pixel pitch	0.271 x 0.264 mm	Weight (with stand)	2.5 kg
Pixel density	94 ppi	Width (without stand)	464.8 mm
Viewable size, vertical	43.3 cm	Depth (without stand)	48.3 mm
Viewable size diagonal	23.8 cm	Height (without stand)	283.5 mm
Colour depth	8 bit	Weight (without stand)	2.2 kg
Colour gamut standard	NTSC	Bezel width (side)	1.53 cm
Colour gamut	72%	Bezel width (top)	1.82 cm
Multimedia		Bezel width (bottom)	2.6 cm
Built-in speaker(s) *	✗	Packaging data	
Built-in camera *	✗	Package width	560 mm
Design		Package depth	125 mm
Market positioning *	Business	Package height	350 mm
Product colour *	Black	Package weight	3.7 kg
Colour name	Raven Black	Packaging content	
Detachable stand	✓	Stand included	✓
Ports & interfaces		Cables included	AC, HDMI
Built-in USB hub *	✗		
VGA (D-Sub) ports quantity	1		

Ports & interfaces		Sustainability	
HDMI *	✓	Sustainability certificates	ENERGY STAR, EPEAT Silver, TCO
HDMI ports quantity	1	Other features	
HDMI version	1.4	Compatible operating systems	Windows 7, Windows 10, Windows 11
Ergonomics		Compliance certificates	RoHS
VESA mounting *	✓	Certification	Energy Star Certified, TCO 9.0, TCO Edge 2.0, EPEAT Silver, RoHS, Volatile Organic Compound
Panel mounting interface	100 x 100 mm		Certification TÜV Rheinland Low Blue Light, TÜV Rheinland Flicker Free
Cable management	✓		
Cable lock slot *	✓		



196119950944

Catalog Object Cloud