

NETGEAR BR500 Kit wired router Gigabit Ethernet White

Brand : NETGEAR

Product code: BRK500-100UKS

Product name : BR500 Kit



- One-step Instant VPN for business protection and remote or site-to-site secure access
 - Easy setup, configuration and instant VPN connectivity from the NETGEAR Insight app or Cloud Portal
 - Stateful Packet Inspection Firewall and easy rule setting for instant protection against intrusion
 - Router setup (DHCP, NAT rules, DMZ ports) from the Insight app or Cloud Portal
 - Full routing capabilities with DHCP, NAT, PPTP, L2TP
 - VPN Business Router with InterVLAN routing, Support for QoS and 802.1q VLANs (256)
 - VLAN in VLAN support (QinQ) for private VLAN tagging in ISP network for an additional layer of isolation and security
 - VPN with SSL Encryption (DES, 3DES, AES)
- Insight Instant 4PT VPN Router Bundle

WAN connection		Security	
Ethernet WAN *	✓	Network address translation (NAT)	✓
DSL WAN *	✗	Features	
SIM card slot *	✗	Built-in processor	✓
3G/4G USB modem compatibility *	✗	Processor frequency	1700 MHz
SFP WAN *	✗	Flash memory	128 MB
Network		Internal memory	1024 MB
Networking standards *	IEEE 802.1Q, IEEE 802.3, IEEE 802.3ab, IEEE 802.3u	Windows operating systems supported	✓
Ethernet interface type *	Gigabit Ethernet	Mac operating systems supported	✓
Cabling technology	10/100/1000Base-T(X)	Linux operating systems supported	✓
Ethernet LAN data rates	10,100,1000 Mbit/s	Safety	CE/LVD, cUL
VLAN support	✓	Certification	FCC 15 B, CE, C-Tick B, VCCI
Port forwarding	✓	Design	
Management features		Product colour *	White
Web-based management *	✓	Power	
Quality of Service (QoS) support	✓	Output voltage	12 V
Universal Plug and Play (UPnP)	✓	Output current	1.5 A
Ports & interfaces		Operational conditions	
Ethernet LAN (RJ-45) ports *	5	Operating temperature (T-T)	0 - 45 °C
Protocols		Storage temperature (T-T)	-20 - 70 °C
DMZ support	✓	Operating relative humidity (H-H)	0 - 90%
Routing protocols	RIP-1, RIP-2	Storage relative humidity (H-H)	0 - 95%
DHCP server *	✓	Weight & dimensions	
Supported network protocols	IPv6	Width	314 mm
Security		Depth	187.5 mm
Security algorithms *	3DES, DES, IPSec, MD5, SHA-1	Height	43.6 mm
Firewall	✓	Weight	1.55 kg
Authentication method	NETGEAR Insight SSO		
URL filtering	✓		
DoS attack prevention	✓		



0606449138252



606449138252

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.