

ASUS VP247HAE computer monitor 59.9 cm (23.6") 1920 x 1080 pixels Full HD LED Black

Brand : ASUS

Product code: 90LM01L0-B05170

Product name : VP247HAE

- 23.6-inch Full HD (1920x1080) LED backlight display with 178°wide viewing angle panel
- ASUS-exclusive SplendidPlus and 3000:1 contrast ratio ensure better image quality
- Robust connectivity including HDMI and D-Sub
- ASUS Eye Care monitors feature TÜV Rheinland-certified Flicker-free and Low Blue Light technologies to ensure a comfortable viewing experience


VP247HAE, 23.6", 16:9, 1920x1080, VA, 5 ms, HDMI, VGA, 561.1x400.1x199.4 mm

ASUS VP247HAE. Display diagonal: 59.9 cm (23.6"), Display resolution: 1920 x 1080 pixels, HD type: Full HD, Display technology: LED, Display surface: Anti-glare, Response time: 5 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. VESA mounting. Product colour: Black



Display		Ergonomics	
Display diagonal *	59.9 cm (23.6")	VESA mounting *	✓
Display resolution *	1920 x 1080 pixels	Panel mounting interface	100 x 100 mm
HD type *	Full HD	Cable lock slot *	✓
Native aspect ratio *	16:9	Cable lock slot type	Kensington
Display technology *	LED	Height adjustment *	✗
Panel type *	VA	Tilt adjustment	✓
Touchscreen *	✗	Tilt angle range	-5 - 20°
Display brightness (typical)	250 cd/m²	Power	
Response time *	5 ms	Energy efficiency class (SDR) *	F
Display surface	Anti-glare	Energy consumption (SDR) per 1000 hours *	20 kWh
Screen shape *	Flat	Power consumption (typical) *	16.8 W
Supported graphics resolutions	640 x 480 (VGA), 720 x 480, 800 x 600 (SVGA), 848 x 480, 1024 x 768 (XGA), 1152 x 864 (XGA+), 1280 x 1024 (SXGA), 1280 x 720 (HD 720), 1280 x 960, 1366 x 768, 1440 x 900 (WXGA+), 1680 x 1050 (WSXGA+), 1920 x 1080 (HD 1080)	Power consumption (off)	0.5 W
		Power consumption (PowerSave)	0.5 W
Contrast ratio (typical) *	3000:1	AC input voltage	100 - 240 V
Contrast ratio (dynamic)	100000000:1	AC input frequency	50 - 60 Hz
Dynamic contrast ratio marketing name	SmartContrast	Energy efficiency scale	A to G
Maximum refresh rate *	75 Hz	Weight & dimensions	
Viewing angle, horizontal	178°	Width (with stand)	561.1 mm
Viewing angle, vertical	178°	Depth (with stand)	199.4 mm
Display number of colours *	16.78 million colours	Height (with stand)	400.1 mm
Pixel pitch	0.2715 x 0.2715 mm	Weight (with stand)	4 kg
Viewable size, horizontal	52.1 cm	Width (without stand)	561.1 mm
Viewable size, vertical	29.3 cm	Depth (without stand)	51.7 mm
Digital horizontal frequency	24 - 83 kHz	Height (without stand)	335.8 mm
Digital vertical frequency	50 - 75 Hz	Weight (without stand)	3.35 kg
NTSC coverage (typical)	75%	Packaging data	
3D	✗	Package width	617 mm
Performance		Package depth	135 mm
NVIDIA G-SYNC *	✗	Package height	457 mm
		Package weight	5.8 kg

Performance		Packaging content	
AMD FreeSync *	✗	Cables included	AC
Flicker-free technology	✓	Quick start guide	✓
Low Blue Light technology	✓	Sustainability	
Multimedia		Sustainability certificates	ENERGY STAR
Built-in speaker(s) *	✗	Other features	
Built-in camera *	✗	On/off switch	✓
Design		Certification	BSMI, CB, CCC, CEL level , CU, ErP, FCC, J-MOSS, KCC, PSB, PSE, UkrSEPRO, UL/cUL, VCCI, WEEE, WHQL (Windows 10, Windows 8.1, Windows 7), MEPS, RCM, TUV, KC
Product colour *	Black	Logistics data	
Feet colour	Black	Harmonized System (HS) code	85285210
Ports & interfaces			
Built-in USB hub *	✗		
VGA (D-Sub) ports quantity	1		
DVI port	✗		
HDMI ports quantity	1		
HDCP	✓		



4712900978506



4718017411011

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.