




APC KVM1116R KVM switch Rack mounting Black

Brand : APC
Product code: KVM1116R
Product name : KVM1116R

- Manage multiple servers with just one keyboard, monitor and mouse
APC KVM1116R - KVM 2G, Digital/IP, 1 Remote/1 Local User, 16 Ports with Virtual Media - FIPS 140-2
APC KVM1116R. Keyboard port type: PS/2, Mouse port type: PS/2, Video port type: VGA. Product colour: Black, Rack capacity: 1U, Certification: C-tick, CE, EAC, FCC Part 15 Class A, ICES-003, TAA compliance, UL-AR, UL 60950-1, VCCI Class A, VDE. AC input frequency: 50 - 60 Hz. Compliance certificates: RoHS. Width: 424 mm, Depth: 188 mm, Height: 43 mm



Ports & interfaces		Sustainability	
Number of computers controlled *	16	Compliance certificates	RoHS
Keyboard port type *	PS/2	Operational conditions	
Mouse port type *	PS/2	Operating temperature (T-T)	0 - 50 °C
Video port type *	VGA	Storage temperature (T-T)	-20 - 60 °C
VGA (D-Sub) ports quantity	1	Operating relative humidity (H-H)	0 - 80%
Network		Storage relative humidity (H-H)	0 - 80%
Ethernet LAN	✓	Weight & dimensions	
Ethernet LAN (RJ-45) ports	1	Width	424 mm
Design		Depth	188 mm
Rack mounting *	✓	Height	43 mm
Rack capacity	1U	Weight	2.59 kg
Product colour *	Black	Packaging data	
Certification	C-tick, CE, EAC, FCC Part 15 Class A, ICES-003, TAA compliance, UL-AR, UL 60950-1, VCCI Class A, VDE	Package width	619 mm
Display		Package depth	330 mm
Built-in display *	✗	Package height	146 mm
Power		Package weight	3.99 kg
AC input frequency	50 - 60 Hz	Logistics data	
		Harmonized System (HS) code	85176200



0731304340195



731304340195

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.