

StarTech.com CFast card to SATA adapter with 2.5" housing

Brand : StarTech.com

Product code: CFAST2SAT25

Product name : CFast card to SATA adapter with 2.5" housing



COR-PRO-SRVC
StarTech.com CFast card to SATA adapter with 2.5" housing. Host interface: SATA, Output interface: CFast. Product colour: Black, Silver, Mean time between failures (MTBF): 50000 h, Certification: CE, FCC, RoHS. Data transfer rate (max): 6 Gbit/s. Supported storage drive heights: 3.3,5 mm. Width: 69 mm, Depth: 99 mm, Height: 10 mm

Ports & interfaces		System requirements	
Host interface *	SATA	Supported storage drive heights	3.3,5 mm
Output interface *	CFast	Technical details	
SATA connector insertion cycles	10000	Compliance certificates	RoHS
Design		Weight & dimensions	
Internal *	✗	Width	69 mm
Product colour	Black, Silver	Depth	99 mm
Mean time between failures (MTBF)	50000 h	Height	10 mm
Certification	CE, FCC, RoHS	Weight	54 g
Features		Packaging data	
Data transfer rate (max)	6 Gbit/s	Screws included	✓
Operational conditions		Quick installation guide	✓
Operating temperature (T-T)	0 - 75 °C	Package width	144 mm
Storage temperature (T-T)	-40 - 85 °C	Package depth	167 mm
Operating relative humidity (H-H)	5 - 95%	Package height	32 mm
		Package weight	100 g
Logistics data			
		Harmonized System (HS) code	84733020
Other features			
		Material	Plastic, Steel



065030861212

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-APR-2026. Prints or copies of Information are only valid on the printed Publication date