

Epson Padlock Singlepack Black 35 DURABrite Ultra Ink

Brand : EpsonProduct family: PadlockProduct code: C13T35814020

Product name : Singlepack
Black 35 DURABrite Ultra Ink

Singlepack Black 35 DURABrite Ultra Ink
Epson Padlock Singlepack Black 35 DURABrite Ultra Ink. Cartridge capacity: Standard Yield, Black ink type: Pigment-based ink, Black ink volume: 16.1 ml, Printing colours: Black, Quantity per pack: 1 pc(s), Black ink page yield: 900 pages



Features		Logistics data	
Black ink type	Pigment-based ink	Pallet gross width	80 cm
Print technology	Inkjet printing	Pallet gross length	120 cm
Compatibility *	- WorkForce Pro WF-4740DTWF -	Pallet gross height	2 m
	WorkForce Pro WF-4730DTWF -	Products per pallet	2400 pc(s)
	WorkForce Pro WF-4725DWF -	Pallet gross weight	0 g
Quantity per pack *	1 pc(s)	Master (outer) case width	120 mm
Black ink cartridges quantity	1	Master (outer) case length	260 mm
Black ink volume	16.1 ml	Master (outer) case height	146 mm
Black ink page yield *	900 pages	Products per master (outer) case	8 pc(s)
Type *	Original	Master (outer) case gross weight	0 g
Cartridge capacity	Standard Yield	Master (outer) case GTIN (EAN/UPC)	8715946632704
Ink type	Pigment-based ink	Harmonized System (HS) code	84439990
Printing colours *	Black	Pallet width (UK)	100 cm
Brand compatibility *	Epson	Pallet length (UK)	120 cm
OEM code	C13T35814020	Pallet height (UK)	2 m
Country of origin	Indonesia	Pallet weight (UK)	0 g
Packaging data		Products per pallet (UK)	2400 pc(s)
Package width	260 mm	Products per pallet layer	240 pc(s)
Package depth	30 mm	Products per pallet layer (UK)	240 pc(s)
Package height	100 mm	Minimum order quantity	8 pc(s)
Package weight	70 g		
Package type	Blister		



8715946632261

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.