

ASUS ProArt PA248CNV computer monitor 61.2 cm (24.1") 1920 x 1200 pixels Full HD+ Black

Brand : ASUS

Product family: ProArt

Product code: 90LM05K1-B03370

Product name : PA248CNV

- 24.1-inch 16:10 WUXGA (1920 x 1200) IPS display with frameless design
 - International color standard 100% sRGB and 100% Rec. 709 wide color gamut
 - Calman Verified with factory calibrated for excellent Delta E < 2 color accuracy
 - Extensive connectivity including DP over USB-C™ with 90W Power Delivery, DisplayPort daisy-chaining, HDMI, USB hub and RJ45 LAN port for the most flexibility
 - 75Hz refresh rate and Adaptive-Sync technology (48~75Hz) to animated content with fast action and eliminate screen tearing
 - VESA wall-mountable and ergonomic design with tilt, swivel, pivot and height adjustments for a comfortable viewing experience
- 24.1" IPS 1920 x 1200, 16:10, 16.7M, 5ms, HDR10, 75Hz, USB-C, DisplayPort, HDMI, 21W, 100 - 240 V, 50/60 Hz



Display		Ports & interfaces	
Display diagonal *	61.2 cm (24.1")	DisplayPort version	1.2
Display resolution *	1920 x 1200 pixels	Headphone out *	✓
HD type *	Full HD+	Headphone outputs	1
Native aspect ratio *	16:10	Headphone connectivity	3.5 mm
Panel type *	IPS	HDCP	✓
Backlight type	LED	HDCP version	1.4
Touchscreen *	✗	Charging port type	USB Type-C
Display brightness (typical)	300 cd/m²	Network	
Response time *	5 ms	Ethernet LAN	✓
Screen shape *	Flat	Ergonomics	
Contrast ratio (typical) *	1000:1	VESA mounting *	✓
Contrast ratio (dynamic)	10000000:1	Panel mounting interface	100 x 100 mm
Dynamic contrast ratio marketing name	ASUS Smart Contrast Ratio (ASCR)	Cable lock slot *	✓
Maximum refresh rate *	75 Hz	Cable lock slot type	Kensington
Viewing angle, horizontal	178°	Height adjustment *	✓
Viewing angle, vertical	178°	Adjustable height (max)	13 cm
Display number of colours *	16.7 million colours	Pivot	✓
Pixel pitch	0.27 x 0.27 mm	Pivot angle	90 - -90°
Pixel density	94 ppi	Swivelling	✓
Viewable size, horizontal	51.8 cm	Swivel angle range	90 - -90°
Viewable size, vertical	32.4 cm	Tilt adjustment	✓
Digital horizontal frequency	30 - 95 kHz	Tilt angle range	35 - -5°
Digital vertical frequency	24 - 75 Hz	Power	
High Dynamic Range (HDR) supported	✓	Energy efficiency class (SDR) *	E
High Dynamic Range (HDR) technology	High Dynamic Range 10 (HDR10)	Energy efficiency class (HDR) *	G
sRGB coverage (typical)	100%		

Performance		Power	
Flicker-free technology	✓	Energy consumption (SDR) per 1000 hours *	19 kWh
Low Blue Light technology	✓	Energy consumption (HDR) per 1000 hours *	22 kWh
Multimedia		Power consumption (typical) *	21 W
Number of speakers	2	Power consumption (PowerSave)	0.5 W
RMS rated power	4 W	AC input voltage	100 - 240 V
Built-in speaker(s) *	✓	AC input frequency	50 - 60 Hz
Built-in camera *	✗	Energy efficiency scale	A to G
Design		Weight & dimensions	
Market positioning *	Graphics design	Width (with stand)	533 mm
Product colour *	Black	Depth (with stand)	211 mm
Feet colour	Silver	Height (with stand)	489 mm
Ports & interfaces		Weight (with stand)	6.5 kg
Built-in USB hub *	✓	Width (without stand)	533 mm
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Depth (without stand)	58 mm
USB upstream port type	USB Type-C	Height (without stand)	359 mm
Number of upstream ports	1	Weight (without stand)	4.4 kg
Number of USB Type-C upstream ports quantity	1	Packaging data	
USB Type-A downstream ports quantity	4	Package width	735 mm
USB Power Delivery (USB PD)	✓	Package depth	177 mm
USB Power Delivery up to	90 W	Package height	442 mm
HDMI *	✓	Package weight	8.5 kg
HDMI ports quantity	1	Packaging content	
HDMI version	1.4	Cables included	AC
DisplayPorts quantity	2	Quick start guide	✓
		Other features	
		RJ-45 ports quantity	1



4711081782230



0195553804448



195553804448

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.