



Lenovo 4XD1J05151 soundbar speaker Black 2.0 channels 4 W

Brand : Lenovo

Product code: 4XD1J05151

Product name : 4XD1J05151

- The front-facing 2 X 2W sound experience is perfect for virtual meetings and online classroom sessions
- Flexible setup by lift functionality to support selected P/T - 30 series monitors and be in the position for your needs
ThinkVision MS30

Lenovo 4XD1J05151 soundbar speaker Black 2.0 channels 4 W:

The ThinkVision MS30 Monitor Soundbar delivers crystal clear and quality sound directly from the front 2 X 2W speakers, so your virtual meetings and classroom experiences are always rich. Its sleek, less than 30mm, modular design is free of cable clutter and pairs perfectly with your ThinkVision P and T Series monitors. It comes with a Security Lock that keeps it safe from physical theft once connected. Lenovo ThinkColour software enables convenient display features for a stress-free experience.



Audio		Features	
Audio output channels *	2.0 channels	Certification	CE; FCC and ICES; CB(62368 -1); KCC; BSMI; VCCI; UKCA; BIS
RMS rated power *	4 W	Ports & interfaces	
Front speaker sensitivity	85 dB	Connectivity technology *	Wired
Soundbar speaker		Bluetooth *	✗
Soundbar speaker RMS power *	4 W	Wi-Fi *	✗
Impedance	4 Ω	USB port	✓
Signal-to-Noise Ratio (SNR)	64 dB	USB 2.0 ports quantity	1
Total Harmonic Distortion (THD)	3%	Weight & dimensions	
Number of woofer drivers	2	Width	256.4 mm
Subwoofer		Depth	34.5 mm
Subwoofer included *	✗	Height	152 mm
Features		Soundbar weight	244 g
Product colour *	Black	Packaging data	
Wall mountable *	✗	Package width	300 mm
Operating temperature (T-T)	-5 - 40 °C	Package depth	70 mm
Operating relative humidity (H-H)	0 - 90%	Package height	80 mm
		Package weight	354 g
		Package type	Box
		Packaging content	
		Number of products included	1 pc(s)



0195892048428



195892048428

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.